


# Pro-Stock™ Panelboard, Unassembled A-Series Lighting Panels

Bolt on, 225 Amperes  
240Vac 1 or 3 Phase or 480Y/277Vac 3 Phase  
Order by Catalog Number from the Customer Service Center

## Expanded Scope Coming Soon. . .

400 & 600A Pro-Stock Panelboards will complete our distributor stock product line....See Merchandised Panelboard page 13-37 for current 400A panel.


Select the interior by the number of circuits and bus type required. Identify the box/front height for use when selecting the box/front catalog number needed.



## Convertible Main Interiors

Interior Type	No. of Circuits	Bus	Feed-thru	Catalog	Box/Front Height	List Price, GO-101P
240Vac, 1-Phase, 3 Wire (THQB Branch Breakers)	18	Cu	Yes	AQU1182RCXAXT1B4	37.5"	\$235.00
	18	Al	Yes	AQU1182RCXAXT1	37.5"	164.00
	18	Cu	No	AQU1182RCXAXB4	31.5"	235.00
	30	Cu	Yes	AQU1302RCXAXT1B4	43.5"	258.00
	30	Al	Yes	AQU1302RCXAXT1	43.5"	190.00
	30	Cu	No	AQU1302RCXAXB4	37.5"	258.00
	42	Cu	Yes	AQU1422RCXAXT1B4	49.5"	306.00
	42	Al	Yes	AQU1422RCXAXT1	49.5"	230.00
	42	Cu	No	AQU1422RCXAXB4	43.5"	306.00
240Vac, 3-Phase, 3 or 4 Wire (THQB Branch Breakers)	18	Cu	Yes	AQU3182RCXAXT1B4	37.5"	235.00
	18	Al	Yes	AQU3182RCXAXT1	37.5"	164.00
	18	Cu	No	AQU3182RCXAXB4	31.5"	235.00
	30	Cu	Yes	AQU3302RCXAXT1B4	43.5"	258.00
	30	Al	Yes	AQU3302RCXAXT1	43.5"	190.00
	30	Cu	No	AQU3302RCXAXB4	37.5"	258.00
	42	Cu	Yes	AQU3422RCXAXT1B4	49.5"	306.00
	42	Al	Yes	AQU3422RCXAXT1	49.5"	230.00
	42	Cu	No	AQU3422RCXAXB4	43.5"	306.00
480Y/277Vac, 3-Phase, 4 Wire (TEY Branch Breakers)	18	Cu	Yes	AEU3182RCXAXT1B4	37.5"	235.00
	18	Al	Yes	AEU3182RCXAXT1	37.5"	164.00
	18	Cu	No	AEU3182RCXAXB4	31.5"	235.00
	30	Cu	Yes	AEU3302RCXAXT1B4	43.5"	258.00
	30	Al	Yes	AEU3302RCXAXT1	43.5"	190.00
	30	Cu	No	AEU3302RCXAXB4	37.5"	258.00
	42	Cu	Yes	AEU3422RCXAXT1B4	49.5"	306.00
	42	Al	Yes	AEU3422RCXAXT1	49.5"	230.00
	42	Cu	No	AEU3422RCXAXB4	43.5"	306.00

## Pro-Stock Interiors Catalog Number Structure



# A Series® Merchandised Panelboards

Order by catalog number from the Customer Service Center.

For branch breakers see section 4-4 through 4-16.

AQ & AE to be replaced by Pro-Stock™.

## Main Lug Interiors

Service	Max. Panel Amps	Branch Attachment Style	Branch Frame Type	Branch Space Required	Aluminum Bus		Copper Bus		Box ①	Front ②
					Catalog Number	List Price GO-103A	Catalog Number	List Price GO-103A		
240V 1P3W	400 TJD	Bolt-On AQ Style	THQB or THHQB	0-30	AQU1304MB	\$ 946.00	AQU1304MBXAXB4	\$1109.00	AB49B or K	AF49F or S
				31-42	AQU1424MB	1107.00	AQU1424MBXAXB4	1391.00	AB55B or K	AF55F or S
		Plug-In AL Style	THQL or THHQL	0-30	ALU1304MB	946.00	—	—	AB49B or K	AF49F or S
				31-42	ALU1424MB	1107.00	—	—	AB55B or K	AF55F or S
240V 3P4W	400 TJD	Bolt-On AQ Style	THQB or THHQB	0-30	AQU3304MB	1068.00	AQU3304MBXAXB4	1357.00	AB49B or K	AF49F or S
				31-42	AQU3424MB	1230.00	AQU3424MBXAXB4	1516.00	AB55B or K	AF55F or S
		Plug-In AL Style	THQL or THHQL	0-30	ALU3304MB	1068.00	—	—	AB49B or K	AF49F or S
				31-42	ALU3424MB	1230.00	—	—	AB55B or K	AF55F or S
480V 3P4W	400 TJD	Bolt-On AE Style	TEY	0-30	AEU3304MB	1344.00	AEU3304MBXAXB4	1628.00	AB49B or K	AF49F or S
				31-42	AEU3424MB	1601.00	AEU3424MBXAXB4	1885.00	AB55B or K	AF55F or S

## Main Breaker Interiors (Main Breaker Included)

Service	Max. Panel Amps	Branch Attachment Style	Branch Frame Type	Branch Space Required	Aluminum Bus		Copper Bus		Box ①	Front ②
					Catalog Number	List Price GO-103A	Catalog Number	List Price GO-103A		
240V 1P3W	400 TJD	Bolt-On AQ Style	THQB or THHQB	0-30	AQU1304CB	\$ 3085.00	AQU1304CBXAXB4	\$3248.00	AB49B or K	AF49F or S
				31-42	AQU1424CB	3237.00	AQU1424CBXAXB4	3521.00	AB55B or K	AF55F or S
		Plug-In AL Style	THQL or THHQL	0-30	ALU1304CB	3085.00	—	—	AB49B or K	AF49F or S
				31-42	ALU1424CB	3237.00	—	—	AB55B or K	AF55F or S
240V 3P4W	400 TJD	Bolt-On AQ Style	THQB or THHQB	0-30	AQU3304CB	3610.00	AQU3304CBXAXB4	3774.00	AB49B or K	AF49F or S
				31-42	AQU3424CB	3757.00	AQU3424CBXAXB4	4043.00	AB55B or K	AF55F or S
		Plug-In AL Style	THQL or THHQL	0-30	ALU3304CB	3606.00	—	—	AB49B or K	AF49F or S
				31-42	ALU3424CB	3757.00	—	—	AB55B or K	AF55F or S
480V 3P4W	400 TJD	Bolt-On AE Style	TEY	0-30	AEU3304BB	4056.00	AEU3304BBXAXB4	4342.00	AB49B or K	AF49F or S
				31-42	AEU3424BB	4301.00	AEU3424BBXAXB4	4590.00	AB55B or K	AF55F or S

- ① Order B for blank endwalls or K for knock-out endwalls
  - ② Order F for flush front or S for surface front
- Panelboards are **not** field convertible from main lug to main breaker.