



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AE110L 110 CFM 1.3 Sones Led Fan/Light

Broan/Nutone LLC

| | |
|------------------|---|
| Catalog Number | AE110L |
| Manufacturer | Broan/Nutone LLC |
| Description | Bath Fan and Light, Ceiling Type; 9-1/4 Inch Length X 10 Inch Width X 5-3/4 Inch Height Size; UL, Hvi Approval; 120 Volt At 60 Hertz Voltage Rating; 0.3 Amp Current Rating; Yes Lamp Included; Led Lamp Type; 11 Watt Lamp Wattage |
| Weight per unit | 9.1 (lbs/each) |
| Product Category | Exhaust Fans |

Features

| | |
|------------------|--|
| Air Flow Rate | 110 CFM |
| Current Rating | 0.3 Amp |
| Duct Shape | Round |
| Duct Size | 4 Inch Diameter |
| Grill Finish | White Polymeric |
| Grill Shape | Rectangular |
| Grill Size | 11-3/4 Inch Length x 12-1/2 Inch Width |
| Housing Shape | Rectangular |
| Lamp Included | Yes |
| Lamp Type | LED |
| Lamp Wattage | 11 Watt |
| Sound Level | 1.3 SONES |
| Ventilation Area | 105 Square Foot |
| Voltage Rating | 120 Volt at 60 Hertz |

Material, Color, and Finish

| | |
|------------------|----------------------------------|
| Housing Material | Rugged 26 Gauge Galvanized Steel |
|------------------|----------------------------------|

Dimensions and Weight

| | |
|------|---|
| Size | 9-1/4 Inch Length x 10 Inch Width x 5-3/4 Inch Height |
|------|---|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Additional Information | Power Rating 23.4 Watt; Number of Speed 1; Includes Permanently Lubricated Plug-In Motor, Tapered Sleeve, Non-Metallic Damper; Excludes Metallic Clatter; Standard Package 1 per pack |
| Commodity Description | Exhaust Fans |
| Description | 110 CFM 1.3 SONES LED FAN/LIGHT |
| extra long description | CEILING TYPE; 9-1/4 INCH LENGTH X 10 INCH WIDTH X 5-3/4 INCH HEIGHT SIZE; UL, HVI APPROVAL; 120 VOLT AT 60 HERTZ VOLTAGE RATING; 0.3 AMP CURRENT RATING; YES LAMP INCLUDED; LED LAMP TYPE; 11 WATT LAMP WATTAGE; RUGGED 26 GAUGE GALVANIZED STEEL HOUSING MATERIAL; 110 CFM AIR FLOW RATE; 4 INCH DIAMETER DUCT SIZE; 1.3 SONES SOUND LEVEL; 11-3/4 INCH LENGTH X 12-1/2 INCH WIDTH GRILL SIZE; RECTANGULAR HOUSING SHAPE; ROUND DUCT SHAPE; RECTANGULAR GRILL SHAPE; WHITE POLYMERIC GRILL FINISH; 105 SQUARE FOOT VENTILATION |
| Long Description | BATH FAN AND LIGHT, CEILING TYPE; 9-1/4 INCH LENGTH X 10 INCH WIDTH X 5-3/4 INCH HEIGHT SIZE; UL, HVI APPROVAL; 120 VOLT AT 60 HERTZ VOLTAGE RATING; 0.3 AMP CURRENT RATING; YES LAMP INCLUDED; LED LAMP TYPE; 11 WATT LAMP WATTAGE |
| Product Type | Bath Fan and Light |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Broan/Nutone LLC |
| GTIN | 00026715236664 |
| Manufacturers Part Number | AE110L |
| UPC | 026715236664 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------|
| Category Description | FANS & HEATERS |
| Type | CEILING |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 9.07 |

Uses, Certifications, and Standards

| | |
|----------|---------|
| Approval | UL, HVI |
|----------|---------|