



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AE110L 110 CFM 1.3 Sones Led Fan/Light

Broan/Nutone LLC

Catalog Number	AE110L
Manufacturer	Broan/Nutone LLC
Description	Bath Fan and Light, Ceiling Type; 9-1/4 Inch Length X 10 Inch Width X 5-3/4 Inch Height Size; UL, Hvi Approval; 120 Volt At 60 Hertz Voltage Rating; 0.3 Amp Current Rating; Yes Lamp Included; Led Lamp Type; 11 Watt Lamp Wattage
Weight per unit	9.1 (lbs/each)
Product Category	Exhaust Fans

Features

Air Flow Rate	110 CFM
Current Rating	0.3 Amp
Duct Shape	Round
Duct Size	4 Inch Diameter
Grill Finish	White Polymeric
Grill Shape	Rectangular
Grill Size	11-3/4 Inch Length x 12-1/2 Inch Width
Housing Shape	Rectangular
Lamp Included	Yes
Lamp Type	LED
Lamp Wattage	11 Watt
Sound Level	1.3 SONES
Ventilation Area	105 Square Foot
Voltage Rating	120 Volt at 60 Hertz

Material, Color, and Finish

Housing Material	Rugged 26 Gauge Galvanized Steel
------------------	----------------------------------

Dimensions and Weight

Size	9-1/4 Inch Length x 10 Inch Width x 5-3/4 Inch Height
------	-------------------------------------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Additional Information	Power Rating 23.4 Watt; Number of Speed 1; Includes Permanently Lubricated Plug-In Motor, Tapered Sleeve, Non-Metallic Damper; Excludes Metallic Clatter; Standard Package 1 per pack
Commodity Description	Exhaust Fans
Description	110 CFM 1.3 SONES LED FAN/LIGHT
extra long description	CEILING TYPE; 9-1/4 INCH LENGTH X 10 INCH WIDTH X 5-3/4 INCH HEIGHT SIZE; UL, HVI APPROVAL; 120 VOLT AT 60 HERTZ VOLTAGE RATING; 0.3 AMP CURRENT RATING; YES LAMP INCLUDED; LED LAMP TYPE; 11 WATT LAMP WATTAGE; RUGGED 26 GAUGE GALVANIZED STEEL HOUSING MATERIAL; 110 CFM AIR FLOW RATE; 4 INCH DIAMETER DUCT SIZE; 1.3 SONES SOUND LEVEL; 11-3/4 INCH LENGTH X 12-1/2 INCH WIDTH GRILL SIZE; RECTANGULAR HOUSING SHAPE; ROUND DUCT SHAPE; RECTANGULAR GRILL SHAPE; WHITE POLYMERIC GRILL FINISH; 105 SQUARE FOOT VENTILATION
Long Description	BATH FAN AND LIGHT, CEILING TYPE; 9-1/4 INCH LENGTH X 10 INCH WIDTH X 5-3/4 INCH HEIGHT SIZE; UL, HVI APPROVAL; 120 VOLT AT 60 HERTZ VOLTAGE RATING; 0.3 AMP CURRENT RATING; YES LAMP INCLUDED; LED LAMP TYPE; 11 WATT LAMP WATTAGE
Product Type	Bath Fan and Light

Manufacturer Information

Brand	Broan/Nutone LLC
GTIN	00026715236664
Manufacturers Part Number	AE110L
UPC	026715236664

Taxonomies, Classifications, and Categories

Category Description	FANS & HEATERS
Type	CEILING

Packaging

Carton	1
Weight Per each	9.07

Uses, Certifications, and Standards

Approval	UL, HVI
----------	---------