



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AE80BL 80CFM Fan W/Led Light 1.5 Sones

Broan/Nutone LLC

Catalog Number	AE80BL
Manufacturer	Broan/Nutone LLC
Description	Bath Fan and Light, Ceiling Type; 9-1/4 Inch Length X 10 Inch Width X 5-3/4 Inch Height Size; UL, Hvi Approval; 120 Volt Voltage Rating; 0.5 Amp Current Rating; Yes Lamp Included; Led Lamp Type; 11 Watt Lamp Wattage
Weight per unit	9.2 (lbs/each)
Product Category	Exhaust Fans

Features

Air Flow Rate	80 CFM
Current Rating	0.5 Amp
Duct Shape	Round
Duct Size	4 Inch Diameter
Grill Finish	White
Grill Shape	Rectangular
Grill Size	11-3/4 Inch Length x 12-1/2 Inch Width
Housing Shape	Rectangular
Lamp Included	Yes
Lamp Type	LED
Lamp Wattage	11 Watt
Sound Level	1.5 SONES
Ventilation Area	75 Square Foot (Bathroom)
Voltage Rating	120 Volt

Material, Color, and Finish

Grill Material	Polymeric
Housing Material	26 Gauge Rugged Galvanized Steel

Dimensions and Weight

Size	9-1/4 Inch Length x 10 Inch Width x 5-3/4 Inch Height
------	---



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Additional Information	Power Rating 26.9 Watt; Includes Grille, Blower, Dimming Control
Commodity Description	Exhaust Fans
Description	80CFM FAN W/LED LIGHT 1.5 SONES
extra long description	CEILING TYPE; 9-1/4 INCH LENGTH X 10 INCH WIDTH X 5-3/4 INCH HEIGHT SIZE; UL, HVI APPROVAL; 120 VOLT VOLTAGE RATING; 0.5 AMP CURRENT RATING; YES LAMP INCLUDED; LED LAMP TYPE; 11 WATT LAMP WATTAGE; 26 GAUGE RUGGED GALVANIZED STEEL HOUSING MATERIAL; 80 CFM AIR FLOW RATE; 4 INCH DIAMETER DUCT SIZE; 1.5 SONES SOUND LEVEL; 11-3/4 INCH LENGTH X 12-1/2 INCH WIDTH GRILL SIZE; POLYMERIC GRILL MATERIAL; RECTANGULAR HOUSING SHAPE; ROUND DUCT SHAPE; RECTANGULAR GRILL SHAPE; WHITE GRILL FINISH; 75 SQUARE FOOT (BATHROOM
Long Description	BATH FAN AND LIGHT, CEILING TYPE; 9-1/4 INCH LENGTH X 10 INCH WIDTH X 5-3/4 INCH HEIGHT SIZE; UL, HVI APPROVAL; 120 VOLT VOLTAGE RATING; 0.5 AMP CURRENT RATING; YES LAMP INCLUDED; LED LAMP TYPE; 11 WATT LAMP WATTAGE
Product Type	Bath Fan and Light

Manufacturer Information

Brand	BROAN
GTIN	00026715239573
Manufacturers Part Number	AE80BL
UPC	026715239573

Taxonomies, Classifications, and Categories

Category Description	FANS & HEATERS
Type	CEILING

Packaging

Carton	1
Weight Per each	9.16

Uses, Certifications, and Standards

Approval	UL, HVI
----------	---------