



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AGC5R 5A 250V 1/4X1-1/4 Rohs Fa Glass Fuse

Bussmann Fuses

Catalog Number	AGC5R
Manufacturer	Bussmann Fuses
Description	Fuse, Fast Acting Fuse Speed, 120/3.6K S Response Time, Ferrule End X Ferrule End Connection, 5 A, 250 V Ac, Glass (Body);Brass(End Cap) Material, Ferrule Terminal, 1/4 In Diameter, 1-1/4 In Overall Length, 0.01 LB
Weight per unit	0.0100 (lbs/each)
Product Category	Small Dimension Fuses

Features

amperage rating	5 A
connection	Ferrule End X Ferrule End
dimensions	1.2500 IN X 0.2500 IN X 0.2500 IN
Response Time	60 min at 135%, 120 sec at 200%

Dimensions and Weight

Size	1/4 In Diameter X 1-1/4 In Length
------	-----------------------------------

Descriptions

Description	5A 250V 1/4X1-1/4 ROHS FA GLASS FUSE
extra long description	EFSE AGC-5-R BUSS SMALL DIMENSION F
Features	Fast-acting, glass tube 1/4" x 1-1/4" ferrule fuse designed to UL 248-14 for overcurrent protection of electronic circuits. Install into a Bussmann Series fuse holder, block, or fuse clip, or purchase with available axial leads for thru-hole installation. Eaton's AGC fast-acting, glass tube 1/4" x 1-1/4" ferrule fuses are designed to UL 248-14 for overcurrent protection of electronic circuits. Order in cartridge fuse format and install into a Bussmann Series fuse holder, block, or fuse clip, or purchase w
Special Features	Interrupt Rating 200 Amp at 250 Vac, 10000 Amp at 125 Vac, Material Glass Tube, Nickel Plated Brass Endcap, ROHS Compliant

Manufacturer Information

Brand	Eaton Bussmann series
GTIN	00051712655231
UPC	051712655231

Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	Fast-acting glass tube fuse



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	5
Weight Per each	0.01

Uses, Certifications, and Standards

standard	CE Marked, RoHS Compliant
----------	---------------------------