



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AGC25R 25A 32V 1/4X1-1/4 Rohs Fa Glass Fuse

Bussmann Fuses

Catalog Number	AGC25R
Manufacturer	Bussmann Fuses
Description	Eaton GBB Series Very Fast-Acting Fuse, 9A, 250 Vac, 125 VDC, R
Weight per unit	0.0100 (lbs/each)
Product Category	Small Dimension Fuses

Features

amperage rating	25 A
connection	Ferrule End X Ferrule End
dimensions	1.2500 IN X 0.2500 IN X 0.2500 IN
interrupt rating	1 kAIC at 32 Vac
Material	Glass tubeNickel-plated brass end cap construction
Response Time	60 min at 135%, 120 sec at 200%
Voltage Rating	32 Vac, 32 Vdc (self certified)

Dimensions and Weight

Size	1/4 In Diameter X 1-1/4 In Length
------	-----------------------------------

Descriptions

Description	25A 32V 1/4X1-1/4 ROHS FA GLASS FUSE
extra long description	BUSS AGC-25-R BUSS SMALL DIMENSION
Features	Fast-acting, glass tube 1/4" x 1-1/4" ferrule fuse designed to UL 248-14 for overcurrent protection of electronic circuits. Install into a Bussmann Series fuse holder, block, or fuse clip, or purchase with available axial leads for thru-hole installation. Eaton's AGC fast-acting, glass tube 1/4" x 1-1/4" ferrule fuses are designed to UL 248-14 for overcurrent protection of electronic circuits. Order in cartridge fuse format and install into a Bussmann Series fuse holder, block, or fuse clip, or purchase w
Long Description	Eaton GBB Series Very fast-acting fuse, 9A, 250 Vac, 125 Vdc, R
Product Type	Buss Small Dimension Fuse
Special Features	Interrupt Rating 1000 Amp at 32 Vac, Material Glass Tube, Nickel Plated Brass Endcap, ROHS Compliant

Manufacturer Information

Brand	Eaton Bussmann series
GTIN	00051712655101
Manufacturers Part Number	AGC-25-R
UPC	051712655101

Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	Fast-acting glass tube fuse



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	5
Weight Per each	0.01

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems
standard	RoHS Compliant,CE Marked