



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AH4100R5W Recp Pin&Sleeve 100A 600V 3PH 3P4W WT BK *Eaton Wiring Devices*

Catalog Number	AH4100R5W
Manufacturer	Eaton Wiring Devices
Description	Eaton Arrow Hart Pin and Sleeve Receptacle, IP69K Rated, #4 -1/0 Awg, #12 - #16 Awg (Pilot), 100A, 3Ø 600V, Back Wire, Black, Nickel Plated Brass, IP67, Nylon, 3-Pole, 4-Wire, AHBB100 Back Box Style, Female, 30 HP, 3PH
Weight per unit	24.0 (lbs/each)
Product Category	Pin & Sleeve Devices

Features

dimensions	7.3750 IN X 7.3750 IN X 6.2500 IN
media	Yes

Descriptions

Description	RECP PIN&SLEEVE 100A 600V 3PH 3P4W WT BK
extra long description	EWD AH4100R5W Recp Pin&Sleeve 100A
Features	Eaton's Arrow Hart full line of pin and sleeve devices offer sturdy nylon construction, rugged design with corrosion resistant components for lasting electrical performance, and watertight sealing that provides IP69K protection so you can feel confident in even the most severe washdown environments.
Long Description	Eaton Arrow Hart pin and sleeve receptacle, IP69K Rated, #4 -1/0 AWG, #12 - #16 AWG (pilot), 100A, 3Ø 600V, Back wire, Black, Nickel plated brass, IP67, Nylon, 3-pole, 4-wire, AHBB100 Back box style, Female, 30 HP, 3PH
Product Type	Recp Pin&Sleeve 100A 600V 3PH 3P4W WT BK
Special Features	Watertight P&S receptacles

Manufacturer Information

Brand	Eaton
GTIN	00040893620572
Manufacturers Part Number	AH4100R5W
UPC	040893620572

Taxonomies, Classifications, and Categories

Category Description	Pin & Sleeve Devices
Type	Pin and Sleeve receptacle

Packaging

Carton	1
Package	8
Weight Per each	24



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application
standard

Ind Facilities & Factories - Facility: Power Distribution and Control
cRUus