



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## AH430P12W Plug Pin&Sleeve 30A 125/250V 3P4W WT or *Eaton Wiring Devices*

Catalog Number	AH430P12W
Manufacturer	Eaton Wiring Devices
Description	Plug Pin and Sleeve 30 Amp 125/250 Volt 3 Pole 4 Wire WT Orange
Weight per unit	24.0 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### Features

amperage rating	30
connection	Pin & Sleeve
dimensions	10.3750 IN X 4.7500 IN X 4.8130 IN
Material	Nylon;Other
media	Yes
Phase	3
Poles	3
Voltage Rating	125/250V/AC
Wire Size	0.433-0.985

### Material, Color, and Finish

Color	Blue & Gray
-------	-------------

### Dimensions and Weight

Size	10.375 x 4.75 x 4.813
------	-----------------------

### Descriptions

Description	PLUG PIN&SLEEVE 30A 125/250V 3P4W WT OR
extra long description	CRS-H AH430P12W PLUG PIN AND SLEEVE
Features	Eaton's Arrow Hart full line of pin and sleeve devices offer sturdy nylon construction, rugged design with corrosion resistant components for lasting electrical performance, and watertight sealing that provides IP69K protection so you can feel confident in even the most severe washdown environments.
Long Description	PLUG PIN AND SLEEVE 30 AMP 125/250 VOLT 3 POLE 4 WIRE WT ORANGE
Product Type	Plug Pin and Sleeve 30A 125/250V 3P4W WT
Special Features	Watertight P&S plugs

### Manufacturer Information

Brand	Eaton
GTIN	00326647323310
Manufacturers Part Number	AH430P12W
UPC	032664732331



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Pin & Sleeve Devices
Type	PLUG

## Packaging

Carton	1
Package	24
Weight Per each	24

## Uses, Certifications, and Standards

Application	IEC 309 Products
environmental conditions	IP67 & IP69k
Mounting	Cable
standard	IEC, UL, CSA