



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AH460P7W Plug Pin&Sleeve 60A 480V 3PH 3P4W WT RD *Eaton Wiring Devices*

Catalog Number	AH460P7W
Manufacturer	Eaton Wiring Devices
Description	Plug Pin and Sleeve 60 Amp 480 Volt 3 Phase 3 Pole 4 Wire WT Red
Weight per unit	24.0 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	60
connection	Pin & Sleeve
dimensions	11.5000 IN X 5.1250 IN X 5.1250 IN
Material	Nylon;Other
media	Yes
Phase	3
Poles	3
Voltage Rating	3Ø 480V/AC
Wire Size	0.66-1.5

Material, Color, and Finish

Color	Blue & Gray
-------	-------------

Dimensions and Weight

Size	11.5 x 5.125 x 5.125
------	----------------------

Descriptions

Description	PLUG PIN&SLEEVE 60A 480V 3PH 3P4W WT RD
extra long description	CRS-H AH460P7W PLUG PIN AND SLEEVE
Features	Eaton's Arrow Hart full line of pin and sleeve devices offer sturdy nylon construction, rugged design with corrosion resistant components for lasting electrical performance, and watertight sealing that provides IP69K protection so you can feel confident in even the most severe washdown environments.
Long Description	PLUG PIN AND SLEEVE 60 AMP 480 VOLT 3 PHASE 3 POLE 4 WIRE WT RED
Product Type	Plug Pin and Sleeve 60A 480V 3PH 3P4W WT
Special Features	Watertight P&S plugs

Manufacturer Information

Brand	Eaton
GTIN	00326647324782
Manufacturers Part Number	AH460P7W
UPC	032664732478



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Pin & Sleeve Devices
Type	PLUG

Packaging

Carton	1
Package	12
Weight Per each	24

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Power Distribution and Control
environmental conditions	IP67 & IP69k
Mounting	Cable
standard	IEC, UL, CSA