



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ALED140M20SANM85 140W Led Area Light 5K T3 & T5 Lens Included

Keystone Technologies

Catalog Number	ALED140M20SANM85
Manufacturer	Keystone Technologies
Description	140W 5000K Led Area Light With Nema Type 3-Pin Twist Lock Receptacle + Shorting Cap. Series 2 Medium Housing. Optics Selectable A (Type Iii and V). 120-277V Input. 0-10V Dimmable. Standard Bronze Housing.
Weight per unit	12.3 (lbs/each)
Product Category	Lighting

Features

Ballast Type	N/A
beam angle	N/A
Circuit Type	N/A
Input Voltage	120-277V
ip rating	IP65
lumens	20900
Nominal Length	N/A
Nominal Size	Medium Housing
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	14
Wire Type	N/A

Material, Color, and Finish

Base Type	N/A
color rendering index (cri)	>80 Deg
color temperature	5000
housing color	Bronze

Descriptions

Construction	N/A
Description	140W LED AREA LIGHT 5K T3 & T5 LENS INCLUDED
extra long description	Key KT-ALED140-M2-OSA-NM-850-VDIM 1
Long Description	140W 5000K LED Area Light with NEMA Type 3-pin Twist Lock Receptacle + Shorting Cap. Series 2 Medium Housing. Optics Selectable A (Type III and V). 120-277V Input. 0-10V Dimmable. Standard Bronze Housing.
Product Type	140W 5000K Led Area Light With Nema Type 3-Pin Twist Lock Re



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Keystone
GTIN	00843654153018
Manufacturers Part Number	KT-ALED140-M2-OSA-NM-850-VDIM
UPC	843654153018

Taxonomies, Classifications, and Categories

Category Description	LED CANOPY, PARKING, POLE MOUNTED & ROADWAY LIGHTING
----------------------	--

Packaging

Carton	1
Weight Per each	12.346

Uses, Certifications, and Standards

Energy Star	N
-------------	---