



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **ALED290PSL20SBSF KT-ALED290PS-L2-Osb-SF-8CSB-Vdim-P** *Keystone Technologies*

Catalog Number	ALED290PSL20SBSF
Manufacturer	Keystone Technologies
Description	290W Power Select Color Select Led Area Light With Nema Type 7-Pin Twist Lock Receptacle + Shorting Cap. Series 2 Large Housing. Optics Selectable B (Type Iii, Iv, and V). Slip Fitter Mount. Nema Type 3-Pin Twist Lock Photocell. 120-277V Input. 0-10V Dimm
Weight per unit	20.2 (lbs/each)
Product Category	Lighting

### Features

Ballast Type	N/A
beam angle	N/A
Circuit Type	N/A
Input Voltage	120-277V
ip rating	IP65
lumens	N/A
Nominal Length	N/A
Nominal Size	Large Housing
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	Photocell
Wattage	290/210/185
Wire Type	N/A

### Material, Color, and Finish

Base Type	N/A
color rendering index (cri)	>80 Deg
color temperature	N/A
housing color	Bronze

### Descriptions

Construction	N/A
Description	KT-ALED290PS-L2-OSB-SF-8CSB-VDIM-P
extra long description	Key KT-ALED290PS-L2-OSB-SF-8CSB-VDI
Long Description	290W Power Select Color Select LED Area Light with NEMA Type 7-pin Twist Lock Receptacle + Shorting Cap. Series 2 Large Housing. Optics Selectable B (Type III, IV, and V). Slip Fitter Mount. NEMA Type 3-pin Twist Lock Photocell. 120-277V Input. 0-10V Dimm
Product Type	290W Power Select Color Select Led Area Light With Nema Type



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Keystone
GTIN	00843654153148
Manufacturers Part Number	KT-ALED290PS-L2-OSB-SF-8CSB-VD
UPC	843654153148

## Taxonomies, Classifications, and Categories

Category Description	LED CANOPY, PARKING, POLE MOUNTED & ROADWAY LIGHTING
----------------------	--

## Packaging

Carton	1
Weight Per each	20.172

## Uses, Certifications, and Standards

Energy Star	N
-------------	---