



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## AL250N 250 Al/Cu 2 Hole Compression Lug

*Nsi Industries*

Catalog Number	AL250N
Manufacturer	Nsi Industries
Description	2HOLESTANDARD Barrelaluminum Compression Lug 250 MCM -1/2 Bolt Standard Barrelaluminum Compression Lugs Is A Type Ofaluminum Compression Connector That Is Produced From High Conductivityaluminum Tubing.Center Stop Assures Proper Cable Installation.They Are Tin-Plated to Provide Corrosion Resistance and Are Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed.
Weight per unit	0.2200 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Cable Size	250 MCM (STR)
Material	Aluminum
Number of Holes	2
Stud Size	1/2
Voltage Rating	600 V
Warranty	1 YEAR

### Material, Color, and Finish

Color	Red
Finish	Tin Plated Bronze

### Dimensions and Weight

Size	L=5.30 - W=1.25 - OD=.920 - ID=.590
------	-------------------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	250 AL/CU 2 HOLE COMPRESSION LUG
extra long description	NSI AL250N AL/CU CMP Lug 4/0 AWG Ne
Features	2HoleStandard BarrelAluminum Compression Lug 250 MCM -1/2 Bolt Standard BarrelAluminum Compression Lugs is a type ofaluminum compression connector that is produced from high conductivityaluminum tubing.Center stop assures proper cable installation.They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Long Description	2HoleStandard BarrelAluminum Compression Lug 250 MCM -1/2 Bolt Standard BarrelAluminum Compression Lugs is a type ofaluminum compression connector that is produced from high conductivityaluminum tubing.Center stop assures proper cable installation.They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Product Type	Al/Cu CMP Lug 4/0 Awg Nema MTG Spacing
Special Features	250 MCM (STR) - 1/2 Mounting Holes - 1 3/4 Hole Spacing

## Manufacturer Information

Brand	NSi
GTIN	00662381031044
Manufacturers Part Number	AL250N
UPC	662381031044

## Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Standard Barrel - Two Hole

## Packaging

Carton	1
Package	12
Weight Per each	0.22

## Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
Mounting	1/2 Mounting Holes
standard	UL486A/B