



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AL600N 600 MCM Al/Cu Crimp

Nsi Industries

Catalog Number	AL600N
Manufacturer	Nsi Industries
Description	2HOLESTANDARD Barrelaluminum Compression Lug 600 MCM -1/2 Bolt Standard Barrelaluminum Compression Lugs Is A Type Ofaluminum Compression Connector That Is Produced From High Conductivityaluminum Tubing.Center Stop Assures Proper Cable Installation.They Are Tin-Plated to Provide Corrosion Resistance and Are Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed.
Weight per unit	0.6400 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Cable Size	600 MCM (STR)
Material	Aluminum
Number of Holes	2
Stud Size	1/2
Voltage Rating	600 V
Warranty	1 YEAR

Material, Color, and Finish

Color	Black
Finish	Tin Plated Bronze

Dimensions and Weight

Size	L=6.74 - W=1.95 - OD=1.44 = ID=.920
------	-------------------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	600 MCM AL/CU CRIMP
extra long description	NSI AL600N 1x500-4 LINE 6x2/0-14 LO
Features	2HoleStandard BarrelAluminum Compression Lug 600 MCM -1/2 Bolt Standard BarrelAluminum Compression Lugs is a type ofaluminum compression connector that is produced from high conductivityaluminum tubing.Center stop assures proper cable installation.They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Long Description	2HoleStandard BarrelAluminum Compression Lug 600 MCM -1/2 Bolt Standard BarrelAluminum Compression Lugs is a type ofaluminum compression connector that is produced from high conductivityaluminum tubing.Center stop assures proper cable installation.They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Product Type	1X500-4 Line 6X2/0-14 Load
Special Features	600 MCM (STR) - 1/2 Mounting Holes - 1 3/4 Hole Spacing

Manufacturer Information

Brand	NSi
GTIN	00662381031099
Manufacturers Part Number	AL600N
UPC	662381031099

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Standard Barrel - Two Hole

Packaging

Carton	1
Package	3
Weight Per each	0.64

Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
Mounting	1/2 Mounting Holes
standard	UL486A/B