




ADJUSTABLE MUD RING, 1 GANG, 3/4"–1 1/2" DRYWALL

CATALOG NUMBER

AMR1224SG



CERTIFICATIONS



FEATURES

Adjustable mud ring accommodates various thicknesses of drywall

Can be adjusted after the installation of drywall

PRODUCT ATTRIBUTES

Material: Steel

Finish: Pregalvanized

Gang: 1

Box Size: 4"

Drywall Thickness: 3/4" - 1 1/2"

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500




Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER



ADJUSTABLE MUD RING, 1 GANG, 3/4"–1 1/2" DRYWALL

CATALOG NUMBER

AMR1224SG



CERTIFICATIONS



FEATURES

Adjustable mud ring accommodates various thicknesses of drywall

Can be adjusted after the installation of drywall

PRODUCT ATTRIBUTES

Material: Steel

Finish: Pregalvanized

Gang: 1

Box Size: 4"

Drywall Thickness: 3/4" - 1 1/2"

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER