



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AN16BNOCC Nema Open 3P STR Size 0 480V Coil

Eaton Corp

Catalog Number	AN16BNOCC
Manufacturer	Eaton Corp
Description	Eaton Freedom Nema Motor Control Starter, Non-Reversing Reset Overload Relay Starter, 1 HP At 115V, 2 HP At 230V, 3 HP At 208, 240V, 5 HP At 480, 600V Maximum Horsepower, 480V/60 HZ or 440V/50 HZ Coil Voltage, 18A, Three-Pole, Size 0
Weight per unit	2.0 (lbs/each)
Product Category	Nema Non-Combination Starters

Features

dimensions	6.0000 IN X 1.9000 IN X 3.4000 IN
Poles	3

Dimensions and Weight

Depth	6
Height	3.4
Size	0
Width	1.9

Descriptions

Description	NEMA OPEN 3P STR SIZE 0 480V COIL
extra long description	ETN AN16BNOCC NEMA size 0 starter w
Features	Eaton's Freedom starters and contactors feature a compact, space-saving design, using state-of-the-art technology and the latest in high strength, impact and temperature resistant insulating materials. In addition to the bimetallic overload, Eaton also offers a series of electronic overload relay (C440) available as a standalone unit and assembled with Freedom contactor.
Long Description	Eaton Freedom NEMA motor control starter, Non-Reversing Reset Overload Relay Starter, 1 hp at 115V, 2 hp at 230V, 3 hp at 208,240V, 5 hp at 480,600V maximum horsepower, 480V/60 Hz or 440V/50 Hz coil voltage, 18A, Three-pole, Size 0
Product Type	Nema Size 0 Starter With 480V Coil
Special Features	Starter w/C306 bi-metal OLR

Manufacturer Information

Brand	Eaton
GTIN	00782113971582
Manufacturers Part Number	AN16BNOCC
UPC	782113971582



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	FREEDOM/NEMA STYLE
Type	Motor control starter

Packaging

Carton	1
Weight Per each	2

Uses, Certifications, and Standards

Application	Stationary Machinery and Equipment Outside Factory - Stationary Machinery and Equipment Outside Factory - Other
Mounting standard	HORIZONTAL CSA Certified,UL Listed