



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ASC20T 2/0 Al/Cu Compression Butt Splice

*Nsi Industries*

Catalog Number	ASC20T
Manufacturer	Nsi Industries
Description	Dual Rated Aluminum Splice 2/0 Awg Dual Rated Aluminum Splices Are A Type Of Aluminum Compression Connector That Is Produced From High Conductivity Aluminum Tubing. Center Stop Assures Proper Cable Installation. Electro-Tin Plated For Corrosion Resistance. Color Coded and Marked With Die Index Information. Pre-Filled With Oxide Inhibitor and Capped With Color Coded Cap.
Weight per unit	0.0600 (lbs/each)
Product Category	Splicing & Terminating Kits

### Features

Material	Aluminum
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR

### Material, Color, and Finish

Color	OLIVE
Finish	Tin Plated Bronze

### Dimensions and Weight

Size	L=2.62 - OD=.689 - ID=.440
------	----------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	2/0 AL/CU COMPRESSION BUTT SPLICE
extra long description	NSI ASC2/0T 2/0 AWG Aluminum Splice
Features	Dual Rated Aluminum Splice 2/0 AWG Dual Rated Aluminum Splices are a type of aluminum compression connector that is produced from high conductivity aluminum tubing. Center stop assures proper cable installation. Electro-tin plated for corrosion resistance. Color coded and marked with die index information. Pre-filled with oxide inhibitor and capped with color coded cap.
Long Description	Dual Rated Aluminum Splice 2/0 AWG Dual Rated Aluminum Splices are a type of aluminum compression connector that is produced from high conductivity aluminum tubing. Center stop assures proper cable installation. Electro-tin plated for corrosion resistance. Color coded and marked with die index information. Pre-filled with oxide inhibitor and capped with color coded cap.
Product Type	2/0 Awg Aluminum Splice - Dual Rated - Olive
Special Features	2/0 AWG (STR) - ALCU Splice

## Manufacturer Information

Brand	NSi
GTIN	00662381032058
Manufacturers Part Number	ASC2/0T
UPC	662381032058

## Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Standard Barrel - ALCU Splice

## Packaging

Carton	12
Weight Per each	0.06

## Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
standard	UL486A/B
Temperature Rating	90 C