



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ASC750T #750 Alum Comp SPLC *Nsi Industries*

Catalog Number	ASC750T
Manufacturer	Nsi Industries
Description	Dual Rated Aluminum Splice 750 MCM Dual Rated Aluminum Splices Are A Type Of Aluminum Compression Connector That Is Produced From High Conductivity Aluminum Tubing. Center Stop Assures Proper Cable Installation. Electro-Tin Plated For Corrosion Resistance. Color Coded and Marked With Die Index Information. Pre-Filled With Oxide Inhibitor and Capped With Color Coded Cap.
Weight per unit	0.7000 (lbs/each)
Product Category	Splicing & Terminating Kits

Features

Material	Aluminum
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR

Material, Color, and Finish

Color	Yellow
Finish	Tin Plated

Dimensions and Weight

Size	L=5.37 - OD=1.60 - ID=1.02
------	----------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	#750 ALUM COMP SPLC
extra long description	NSI ASC750T 750 MCM Aluminum Splice
Features	Dual Rated Aluminum Splice 750 MCM Dual Rated Aluminum Splices are a type of aluminum compression connector that is produced from high conductivity aluminum tubing. Center stop assures proper cable installation. Electro-tin plated for corrosion resistance. Color coded and marked with die index information. Pre-filled with oxide inhibitor and capped with color coded cap.
Long Description	Dual Rated Aluminum Splice 750 MCM Dual Rated Aluminum Splices are a type of aluminum compression connector that is produced from high conductivity aluminum tubing. Center stop assures proper cable installation. Electro-tin plated for corrosion resistance. Color coded and marked with die index information. Pre-filled with oxide inhibitor and capped with color coded cap.
Product Type	750 MCM Aluminum Splice - Dual Rated - Yellow
Special Features	750 MCM (STR) - ALCU Splice

Manufacturer Information

Brand	NSi
GTIN	00662381032140
Manufacturers Part Number	ASC750T
UPC	662381032140

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Standard Barrel - ALCU Splice

Packaging

Carton	1
Package	3
Weight Per each	0.7

Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
standard	UL486A/B
Temperature Rating	90 C