



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ASC750T #750 Alum Comp SPLC *Nsi Industries*

| | |
|------------------|--|
| Catalog Number | ASC750T |
| Manufacturer | Nsi Industries |
| Description | Dual Rated Aluminum Splice 750 MCM Dual Rated Aluminum Splices Are A Type Of Aluminum Compression Connector That Is Produced From High Conductivity Aluminum Tubing. Center Stop Assures Proper Cable Installation. Electro-Tin Plated For Corrosion Resistance. Color Coded and Marked With Die Index Information. Pre-Filled With Oxide Inhibitor and Capped With Color Coded Cap. |
| Weight per unit | 0.7000 (lbs/each) |
| Product Category | Splicing & Terminating Kits |

Features

| | |
|----------------------|----------|
| Material | Aluminum |
| Number of Conductors | 2 |
| Poles | 1 |
| Voltage Rating | 600 V |
| Warranty | 1 YEAR |

Material, Color, and Finish

| | |
|--------|------------|
| Color | Yellow |
| Finish | Tin Plated |

Dimensions and Weight

| | |
|------|----------------------------|
| Size | L=5.37 - OD=1.60 - ID=1.02 |
|------|----------------------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|--|
| Description | #750 ALUM COMP SPLC |
| extra long description | NSI ASC750T 750 MCM Aluminum Splice |
| Features | Dual Rated Aluminum Splice 750 MCM Dual Rated Aluminum Splices are a type of aluminum compression connector that is produced from high conductivity aluminum tubing. Center stop assures proper cable installation. Electro-tin plated for corrosion resistance. Color coded and marked with die index information. Pre-filled with oxide inhibitor and capped with color coded cap. |
| Long Description | Dual Rated Aluminum Splice 750 MCM Dual Rated Aluminum Splices are a type of aluminum compression connector that is produced from high conductivity aluminum tubing. Center stop assures proper cable installation. Electro-tin plated for corrosion resistance. Color coded and marked with die index information. Pre-filled with oxide inhibitor and capped with color coded cap. |
| Product Type | 750 MCM Aluminum Splice - Dual Rated - Yellow |
| Special Features | 750 MCM (STR) - ALCU Splice |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | NSi |
| GTIN | 00662381032140 |
| Manufacturers Part Number | ASC750T |
| UPC | 662381032140 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type | Standard Barrel - ALCU Splice |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Package | 3 |
| Weight Per each | 0.7 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Terminate, Splice, Tap Power Connectors |
| environmental conditions | 90 C |
| standard | UL486A/B |
| Temperature Rating | 90 C |