



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ATM20 20A 32VDC Automotive Mini

Bussmann Fuses

Catalog Number	ATM20
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series Atm Blade Fuse, Color Code Yellow, 32 VDC, 20A, 1 Kaic, Non Indicating, Blade Fuse, Blade End, Colored Plastic Housing, Zinc Fuse Element
Weight per unit	0.0120 (lbs/each)
Product Category	Tools & Testers

Features

amperage rating	20 Amp
connection	Blade End
dimensions	1.3800 IN X 0.4400 IN X 1.6000 IN
interrupt rating	1000 Amp
Material	Zinc fuse elementColored plastic housing
media	Yes
type of indicators	Non-Indicating
Voltage Rating	32 VDC

Dimensions and Weight

Size	0.430 In Width X 0.15 In Depth X 0.606 In Height
------	--

Descriptions

Description	20A 32VDC AUTOMOTIVE MINI
extra long description	BUSS ATM-20 ATM MINI BLADE FUSE - 2
Features	Automotive blade fuses are the industry standard - used in most domestic and imported cars today. All Bussmann series blade fuses meet or exceed OEM and SAE standards. The easyID indicating blade fuses use LED technology making it easier to spot blown fuses in panels tucked in dark locations.
Long Description	Eaton Bussmann series ATM blade fuse, Color code yellow, 32 Vdc, 20A, 1 kAIC, Non Indicating, Blade fuse, Blade end, Colored plastic housing, zinc fuse element
Product Type	Atm Mini Blade Fuse - 20 Amp (5 In Tin)
Special Features	Color Yellow

Manufacturer Information

Brand	Eaton Bussmann series
GTIN	00051712814652
Manufacturers Part Number	ATM-20
UPC	051712814652



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description Fuses & Fuse Accessories

Type Blade fuse

Packaging

Carton 5

Weight Per each 0.012

Uses, Certifications, and Standards

Application Vehicles: On-Road

standard RoHS Compliant,Contact factory