



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## AV3ATCBK A/V FL Poke-Thru Assy/20A/BK/TC *Wiremold/Legrand*

Catalog Number	AV3ATCBK
Manufacturer	Wiremold/Legrand
Description	A/V Device Includes One Prewired 20A Duplex Receptacle Which Can Be Wired As A Standard Receptacle or Isolated Ground. Finish Flange Available In Gray (Gy), Black (BK), Ivory (Vy), Brushed Aluminum (Al) and Brass Finish (BS). Aluminum and Brass Flanges Standard With Black Cover. Aluminum Flange Also Available With An Aluminum Colored Nonmetallic Cover (AA). Brass Flange Also Available With Brass Colored Nonmetallic Cover (Ab). Includes One Adapter to Accept Legrand Avip or Extron Electronics Maap Mini Arch
Weight per unit	6.6 (lbs/each)
Product Category	Floor Boxes & Accessories

### Features

fire rating	2 hr
Knockout Size	1-1/4 in, 3/4 in
Number of Knockouts	2
Number of Outlets	2.0

### Material, Color, and Finish

Color	Black
-------	-------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	A/V FL POKE-THRU ASSY/20A/BK/TC
extra long description	WLK AV3ATCBK A/V FL POKE-THRU ASSY/
Features	A/V device includes one prewired 20A duplex receptacle which can be wired as a standard receptacle or isolated ground. Finish flange available in gray (GY), black (BK), ivory (VY), brushed aluminum (AL) and brass finish (BS). Aluminum and brass flanges standard with black cover. Aluminum flange also available with an aluminum colored nonmetallic cover (AA). Brass flange also available with brass colored nonmetallic cover (AB). Includes one adapter to accept Legrand AVIP or Extron Electronics MAAP mini arch
Long Description	A/V device includes one prewired 20A duplex receptacle which can be wired as a standard receptacle or isolated ground. Finish flange available in gray (GY), black (BK), ivory (VY), brushed aluminum (AL) and brass finish (BS). Aluminum and brass flanges standard with black cover. Aluminum flange also available with an aluminum colored nonmetallic cover (AA). Brass flange also available with brass colored nonmetallic cover (AB). Includes one adapter to accept Legrand AVIP or Extron Electronics MAAP mini arch
Product Type	A/V FL Poke-Thru Assy/20A/BK/TC
Special Features	TopGuard Protection, Dual Service, Audio/Visual compatible, slide door activation

## Manufacturer Information

Brand	WIREMOLD
GTIN	00786564015598
Manufacturers Part Number	AV3ATCBK
UPC	786564015598

## Taxonomies, Classifications, and Categories

Category Description	Panduit & Wiremold Metallic & Non-Metallic Raceways
Type	Poke-Thru

## Packaging

Carton	1
Weight Per each	6.619

## Uses, Certifications, and Standards

standard	CULUS, ROHS, UL Fire Classified, cULus, NEC
----------	---