



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ATQ15 500V 15A TD Midget Fuse

Mersen Fuses

Catalog Number	ATQ15
Manufacturer	Mersen Fuses
Description	Fuse Atq - Midget - Time-Delay 500VAC 15A Ferrule Amp-Trap®
Weight per unit	0.0120 (lbs/each)
Product Category	Small Dimension Fuses

Features

AC Voltage Rating	500
amperage rating	15
class	Midget
connection	Ferrule
interrupt rating	10
Voltage Rating	500

Material, Color, and Finish

Body Material	GMG
---------------	-----

Dimensions and Weight

Size	1.5 x 0.41
------	------------

Descriptions

Description	500V 15A TD MIDGET FUSE
extra long description	Mersen ATQ15 Fuse ATQ - Midget - Ti
Features	Amp-Trap ATQ midget time-delay fuses are rated 500VAC with 42 ampere ratings from 1/10 to 30A. They are an excellent choice for supplemental protection of circuits where the available short circuit current does not exceed 10,000A. (Not for Branch Circuit Protection)
Long Description	Fuse ATQ - Midget - Time-Delay 500VAC 15A Ferrule Amp-Trap®
Product Type	Fuse Atq - Midget - Time-Delay 500VAC 15A Ferrule
Short Description	500V 15A TD MIDGET FUSE
Special Features	Numerous ratings for a wide variety of applications up to 500VAC Time-delay (12 seconds at 200 percent rating) for circuits with high inrush current Can be used with UltraSafe™ Fuse holders 1 1/2" x 13/32" (10 mm x 38 mm) dimensions

Manufacturer Information

Brand	Mersen
GTIN	00782001904609
Manufacturers Part Number	ATQ15
UPC	782001904609



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	MIDGET FUSES
Type	Midget Fuses

Packaging

Carton	1
Package	10
Weight Per each	0.012

Uses, Certifications, and Standards

Application	Supplemental protection of lighting, solenoid, motor and transformer circuits
Mounting standard	Clip UL listed to standard 248-14 File E33925 CSA Certified to Standard C22.2 No. 248.14