



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AYLV600PHWH Ariadni 450W Magnetic Low Voltage SP White Clam *Lutron*

Catalog Number	AYLV600PHWH
Manufacturer	Lutron
Description	Ariadni Dimmer, Magnetic Low-Voltage, Single-Pole, Preset, 120V/600VA (450W) Clamshell Packaging In White
Weight per unit	0.2500 (lbs/each)
Product Category	Lighting Dimmers

Features

actuator	Toggle Switch
connection	Screw Terminal
Connection Type	Screw Terminal
insulation	Plastic
Material	Plastic/Metal
media	Yes
Poles	1
Switch Type	Toggle
Voltage Rating	120
Wattage	450

Material, Color, and Finish

Color	White
-------	-------

Dimensions and Weight

Size	4.60 x 2.86;117 x 73
------	----------------------

Descriptions

Description	ARIADNI 450W MAGNETIC LOW VOLTAGE SP WHITE CLAM
extra long description	LUT AYLV-600PH-WH ARIADNI LOW VOLT
Long Description	Ariadni Dimmer, Magnetic Low-Voltage, Single-pole, preset, 120V/600VA (450W) clamshell packaging in white
Product Type	Ariadni Low Volt 600VA Preset WH Clam
Special Features	Controls 600 VA (450 W) magnetic low-voltage loads. Toggle turn lights on/off. Slide up to brighten, down to dim.

Manufacturer Information

Brand	Lutron
GTIN	00027557510219
Manufacturers Part Number	AYLV600PHWH
UPC	027557510219

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Preset dimmer, single-pole, clamshell packaging



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	6
Package	1
Weight Per each	0.25

Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
environmental conditions	Indoor use only
Frequency Rating	50 to 60
Mounting	WALLBOX
Operating Temperature	32 to 104
standard	UL, cUL