



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **B2008PAHDGWSS6 BLTF 1/2" HDG Pa Pipe Clamp W/SS6 HW**

*Cooper B-Line/Cable Tray*

|                  |   |
|------------------|---|
| Catalog Number   | B2008PAHDGWSS6  |
| Manufacturer     | Cooper B-Line/Cable Tray  |
| Description      | Eaton B-Line Series Strut Pipe Clamps and Accessories, .06" Height, 2.396" Length, 1.25" Width, Steel, Include Combination Recess Hex Head Machine Screw, Hot-Dipped Galvanized |
| Weight per unit  | 0.1100 (lbs/each)   |
| Product Category | Channel & Strut Fittings  |

### **Features**

|                 |   |
|-----------------|---|
| amperage rating | Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other |
| dimensions      | NEMA,CSA C22.2.,UL 508A   |
| Material        | Low-Carbon Steel  |
| Response Time   | NEMA,CSA C22.2.,UL 508A   |

### **Material, Color, and Finish**

|        |   |
|--------|---|
| Color  | Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other |
| Finish | Hot-Dip Galvanize   |

### **Dimensions and Weight**

|      |   |
|------|---|
| Size | Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other |
|------|---|

### **Descriptions**

|                        |   |
|------------------------|---|
| Construction           | TWO PIECE   |
| Description            | BLTF 1/2" HDG PA PIPE CLAMP W/SS6 HW  |
| extra long description | B-LINE B2008PAHDGW/SS6 1/2" PIPE/CO   |
| Features               | Eaton offers a wide variety of B-Line series pipe clamps and accessories used for the support and attachment of pipe to structural members.                                     |
| Long Description       | Eaton B-Line series strut pipe clamps and accessories, .06" height, 2.396" length, 1.25" width, Steel, Include combination recess hex head machine screw, Hot-dipped galvanized |
| Product Type           | 1/2" Pipe/Conduit Clamp, Rigid, 1/2", Pre-Asm, HD Glvani  |
| Special Features       | Includes Combination Recess Hex Head Machine Screw and Square Nut, With 316 Stainless Steel Hardware  |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|                           |   |
|---------------------------|---|
| Brand                     | EATON B-LINE SERIES   |
| GTIN                      | 00781011928438  |
| Manufacturers Part Number | B2008PAHDGW/SS6   |
| sub brand                 | Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other |
| UPC                       | 781011928438  |

## Taxonomies, Classifications, and Categories

|                      |                                   |
|----------------------|-----------------------------------|
| Category Description | BEAM, RA, EDGE, & PARALLEL CLAMPS |
| Type                 | Pipe clamps and accessories       |

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 100  |
| Weight Per each | 0.11 |

## Uses, Certifications, and Standards

|             |  |
|-------------|--|
| Application | Stationary Mach Equip In Factory - RoboticsElec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMsElec Assemblies, Panels & OEM - Elec Assemblies/Panels/OEMs - AftermarketElec Assemblies, Panels & OEM - Control Panels for MachinesElec Assemblies, Panels & OEM - Panel BuildersInd Facilities & Factories - Facility: Power Distribution and ControlElec Assemblies, Panels & OEM - Electrical Assemblies and OEMs - Other |
| Mounting    | Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other  |
| standard    | Not Applicable   |