



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BAB1025 Type Bab Circuit BRKR, 1P, 25AMP, 40C, 120/240V, 10, 000

Eaton Corp

Catalog Number	BAB1025
Manufacturer	Eaton Corp
Description	Eaton Bab Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, High Intensity Discharge, 25 A, 10 Kaic, Single-Pole, 120/240 V, Non-Interchangeable, Q7, Bab
Weight per unit	0.3500 (lbs/each)
Product Category	1 Pole Standard Trip Bolt-On

Features

dimensions	4.0000 IN X 1.0000 IN X 5.0000 IN
interrupt rating	10
media	Yes
Poles	1
Voltage Rating	120/240 V

Descriptions

Description	TYPE BAB CIRCUIT BRKR,1P,25AMP,40C,120/240V,10,000
extra long description	ETN BAB1025 BAB ,1P,25AMP,40C,120/2
Features	Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15–100A are HACR rated. Select from one-, two-, or three-pole designs.
Long Description	Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,High intensity discharge,25 A,10 kAIC,Single-pole,120/240 V,Non-Interchangeable,Q7,BAB
Product Type	Bab , 1P, 25AMP, 40C, 120/240V, 10ka
Special Features	High intensity discharge

Manufacturer Information

Brand	Eaton Corp
GTIN	00786679301258
Manufacturers Part Number	BAB1025
UPC	786679301258

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Weight Per each	0.35



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Datacenters - IT Space: CI and Hyper Converged
Marine Vessels and Equipment - Marine Vessels and Equipment -
Other
Other Generation - Renewable Energy - Alternative
Energy Generation - Conventional Energy - Conventional
Energy Residential Bldgs & Facilities - Residential Bldgs & Facilities
- Other

standard

CSA Certified, UL Listed