



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BAB2090 BAB2090 BRKR A

Eaton Corp

Catalog Number	BAB2090
Manufacturer	Eaton Corp
Description	Eaton Bab Thermal Magnetic Circuit Breaker, 90A, Bab Type, 10 Kaic, Bolt-On Mounting, Two-Pole, Non-Interchangeable, 120/240V
Weight per unit	0.7400 (lbs/each)
Product Category	2 Pole Standard Trip Bolt-On

Features

dimensions	3.5000 IN X 2.5000 IN X 3.0000 IN
interrupt rating	10
media	Yes
Poles	2
Voltage Rating	120/240 V

Descriptions

Description	BAB2090 BRKR A
extra long description	ETN BAB2090 90A, 2 pole circuit bre
Features	Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15-100A are HACR rated. Select from one-, two-, or three-pole designs.
Long Description	Eaton BAB thermal magnetic circuit breaker, 90A, BAB type, 10 kAIC, Bolt-on mounting, Two-pole, Non-Interchangeable, 120/240V
Product Type	90A, 2 Pole Circuit Breaker, Pow-R-Line
Special Features	Bolt-on mounting

Manufacturer Information

Brand	Eaton
GTIN	00786679302903
Manufacturers Part Number	BAB2090
UPC	786679302903

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Weight Per each	0.74



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Generation - Renewable Energy - Alternative Energy
Generation - Conventional Energy - Conventional Energy
Other Marine Vessels and Equipment - Marine Vessels and Equipment -
Other Datacenters - IT Space: CI and Hyper Converged
Residential Bldgs & Facilities - Residential Bldgs & Facilities - Other

standard

CSA Certified, UL Listed