



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BAB3035H BAB3035H BRKR A

Eaton Corp

Catalog Number	BAB3035H
Manufacturer	Eaton Corp
Description	Eaton Bab Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, 35 A, 10 Kaic, Three-Pole, 240 V, Non-Interchangeable, Bab, 120-240 V Shunt Trip
Weight per unit	1.0 (lbs/each)
Product Category	3 Pole Standard Trip Bolt-On

Features

dimensions	3.3750 IN X 3.0000 IN X 3.2500 IN
interrupt rating	10
Poles	3
Voltage Rating	240 V - 240 V

Descriptions

Description	BAB3035H BRKR A
extra long description	ETN BAB3035H 35A, 3 pole circuit br
Features	Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15-100A are HACR rated. Select from one-, two-, or three-pole designs.
Long Description	Eaton BAB thermal magnetic circuit breaker, Quicklag industrial thermal-magnetic circuit breaker, 35 A, 10 kAIC, Three-pole, 240 V, Non-interchangeable, BAB, 120-240 V Shunt trip
Product Type	35A, 3 Pole Circuit Breaker, Pow-R-Line
Special Features	Bolt-on mounting

Manufacturer Information

Brand	Eaton
GTIN	00786679303351
Manufacturers Part Number	BAB3035H
UPC	786679303351

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Package	8
Weight Per each	1



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Datacenters - IT Space: CI and Hyper Converged
Other Generation
- Conventional Energy - Conventional Energy
Generation -
Renewable Energy - Alternative Energy
Marine Vessels and
Equipment - Marine Vessels and Equipment - Other
Residential
Bldgs & Facilities - Residential Bldgs & Facilities - Other

standard

UL Listed, CSA Certified