



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **BAB2020 BRKR A BAB2020~1230C41G12~1230C41G02~BRKR A**

*Eaton Corp*

Catalog Number	BAB2020
Manufacturer	Eaton Corp
Description	Eaton Bab Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, Bolt-On Mounting, Switching Neutral, 20 A, 10 Kaic, Two-Pole, 120/240 V, Non-Interchangeable, Q7, Bab
Weight per unit	1.0 (lbs/each)
Product Category	2 Pole Standard Trip Bolt-On

### **Features**

dimensions	2.9060 IN X 2.0000 IN X 2.9060 IN
interrupt rating	10
Poles	2
Voltage Rating	120/240 V

### **Descriptions**

Description	BRKR A BAB2020~1230C41G12~1230C41G02~BRKR A
extra long description	ETN BAB2020 20A, 2 pole circuit bre
Features	Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15–100A are HACR rated. Select from one-, two-, or three-pole designs.
Long Description	Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,Bolt-on mounting, Switching neutral,20 A,10 kAIC,Two-pole,120/240 V,Non-Interchangeable,Q7,BAB
Product Type	20A, 2 Pole Circuit Breaker, Pow-R-Line
Special Features	Bolt-on mountingSwitching neutral

### **Manufacturer Information**

Brand	Eaton
GTIN	00786679302200
Manufacturers Part Number	BAB2020
UPC	786679302200

### **Taxonomies, Classifications, and Categories**

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

### **Packaging**

Carton	1
Weight Per each	1.03



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

OtherGeneration - Conventional Energy - Conventional  
EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine  
Vessels and Equipment - Marine Vessels and Equipment -  
OtherGeneration - Renewable Energy - Alternative  
EnergyResidential Bldgs & Facilities - Residential Bldgs & Facilities  
- Other

standard

UL Listed,CSA Certified