



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BAB2080 BAB20 80 BKR A

Eaton Corp

Catalog Number	BAB2080
Manufacturer	Eaton Corp
Description	Eaton Bab Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, Bolt-On Mounting, 80 A, 10 Kaic, Two-Pole, 240 V, Non-Interchangeable, Q7, Bab
Weight per unit	0.7000 (lbs/each)
Product Category	2 Pole Standard Trip Bolt-On

Features

dimensions	3.9000 IN X 2.2000 IN X 4.8000 IN
interrupt rating	10
media	Yes
Poles	2
Voltage Rating	120/240 V

Descriptions

Description	BAB20 80 BKR A
extra long description	ETN BAB2080 BAB 2 pole 80 amp break
Features	Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15–100A are HACR rated. Select from one-, two-, or three-pole designs.
Long Description	Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,Bolt-on mounting,80 A,10 kAIC,Two-pole,240 V,Non-Interchangeable,Q7,BAB
Product Type	Bab 2 Pole 80 Amp Breaker
Special Features	Bolt-on mounting

Manufacturer Information

Brand	Eaton Corp
GTIN	00786679302804
Manufacturers Part Number	BAB2080
UPC	786679302804

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Weight Per each	0.7



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Datacenters - IT Space: CI and Hyper Converged
Generation - Conventional Energy - Conventional Energy
Other Marine Vessels and Equipment - Marine Vessels and Equipment -
Other Generation - Renewable Energy - Alternative
Energy Residential Bldgs & Facilities - Residential Bldgs & Facilities
- Other

standard

CSA Certified, UL Listed