



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## BAB3045H 45A 3POLE Circuit Breaker Pow-R-Line

Eaton Corp

Catalog Number	BAB3045H
Manufacturer	Eaton Corp
Description	Eaton Bab Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, Moisture-Fungus Treatment, 45 A, 10 Kaic, Three-Pole, 240 V, Non-Interchangeable, Q32, Bab
Weight per unit	9.0 (lbs/each)
Product Category	3 Pole Standard Trip Bolt-On

### Features

amperage rating	45 A
dimensions	3.5000 IN X 3.0000 IN X 3.5000 IN
interrupt rating	10
media	Yes
Poles	3
Trip Type	Non-Interchangeable
Voltage Rating	240 V - 240 V

### Descriptions

Description	45A 3POLE CIRCUIT BREAKER POW-R-LINE
extra long description	ETN BAB3045H 45A, 3 pole circuit br
Features	Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15–100A are HACR rated. Select from one-, two-, or three-pole designs.
Long Description	Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,Moisture-fungus treatment,45 A,10 kAIC,Three-pole,240 V,Non-Interchangeable,Q32,BAB
Product Type	45A, 3 Pole Circuit Breaker, Pow-R-Line
Special Features	Bolt-on mounting

### Manufacturer Information

Brand	Eaton
GTIN	00786679303450
Manufacturers Part Number	BAB3045H
UPC	786679303450

### Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	8
Weight Per each	9

## Uses, Certifications, and Standards

Application	Marine Vessels and Equipment - Marine Vessels and Equipment - OtherOtherGeneration - Renewable Energy - Alternative EnergyGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper ConvergedResidential Bldgs & Facilities - Residential Bldgs & Facilities - Other
standard	UL Listed,CSA Certified