

## Cable To Wire and Rod Fasteners

- Supports cable from #12 wire thru 3/8" threaded rod.
- Cable retainer clips are included with hooks.
- W2 series attaches to #12 wire thru 1/4" plain or threaded rod.
- W6 series attaches to 3/8" plain or threaded rod.
- Static Load Capacity: 25 Lbs.
- Finish: Pre-Galvanized.


Communication & Low Voltage



UPC/Part Number	Catalog Number	Description	Box Qty.
78205146573	<b>BCH12-W2</b>	3/4"	50
78101104819	<b>BCH21-W2</b>	1 <sup>5</sup> / <sub>16</sub> "	50
78101104841	<b>BCH32-W2</b>	2"	50
78205128082	<b>BCH12-W6</b>	3/4"	50
78101195567	<b>BCH21-W6</b>	1 <sup>5</sup> / <sub>16</sub> "	50
78101195569	<b>BCH32-W6</b>	2"	50

(See pages 235-236 for technical data.)

*Read safety/installation instruction sheets in packages before use.*



## Cable To T-Bar Fasteners


- Supports cable above ceiling grid and allows 360° rotation.
- Provides compliance with the EIA/TIA requirements.
- Permits dropwire attachment if required.
- Cable retainer clips are included with hooks.
- Static Load Capacity: 30 Lbs.
- Finish: Pre-Galvanized.



UPC/Part Number	Catalog Number	Description	Box Qty.
78205128083	<b>BCH12-A28</b>	3/4"	50
78101104857	<b>BCH21-A28</b>	15/16"	50
78101104858	<b>BCH32-A28</b>	2"	50

(See pages 235-236 for technical data.)

Read safety/installation instruction sheets in packages before use.



## Cable To Wire and Rod Fasteners

- Supports cable from #12 wire thru  $\frac{3}{8}$ " threaded rod.
- Cable retainer clips are included with hooks.
- W2 series attaches to #12 wire thru  $\frac{1}{4}$ " plain or threaded rod.
- W6 series attaches to  $\frac{3}{8}$ " plain or threaded rod.
- Static Load Capacity: 25 Lbs.
- Finish: Pre-Galvanized.


Communication & Low Voltage



UPC/Part Number	Catalog Number	Description	Box Qty.
78205146573	<b>BCH12-W2</b>	$\frac{3}{4}$ "	50
78101104819	<b>BCH21-W2</b>	$1\frac{5}{16}$ "	50
78101104841	<b>BCH32-W2</b>	2"	50
78205128082	<b>BCH12-W6</b>	$\frac{3}{4}$ "	50
78101195567	<b>BCH21-W6</b>	$1\frac{5}{16}$ "	50
78101195569	<b>BCH32-W6</b>	2"	50

(See pages 235-236 for technical data.)

*Read safety/installation instruction sheets in packages before use.*



## Cable To T-Bar Fasteners

- Supports cable above ceiling grid and allows 360° rotation.
- Provides compliance with the EIA/TIA requirements.
- Permits dropwire attachment if required.
- Cable retainer clips are included with hooks.
- Static Load Capacity: 30 Lbs.
- Finish: Pre-Galvanized.



UPC/Part Number	Catalog Number	Description	Box Qty.
78205128083	<b>BCH12-A28</b>	3/4"	50
78101104857	<b>BCH21-A28</b>	15/16"	50
78101104858	<b>BCH32-A28</b>	2"	50

(See pages 235-236 for technical data.)

Read safety/installation instruction sheets in packages before use.