

# Eaton BKHFD150

Catalog Number: BKHFD150

Eaton Pow-R-stock series Main circuit breaker kit, HFD circuit bkr type, Top and Bottom Mounting, Top and Bottom, Single- or three-phase, 150A



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Pow-R-Stock main breaker kit	BKHFD150
<b>UPC</b>	<b>Product Length/Depth</b>
786689030780	3.9 in
<b>Product Height</b>	<b>Product Width</b>
6 in	4.13 in
<b>Product Weight</b>	<b>Certifications</b>
5 lb	UL Listed

## defaultTaxonomyAttributeLabel

### Circuit breaker type

HFD

### Mounting

Top, bottom

### Phase

Single-phase, three-phase

### Rated operational current

150A

### Series

Pow-R-stock

## Resources

### Multimedia

[Pow-R-Line Xpert family overview](#)

### Specifications and datasheets

[Eaton Specification Sheet - BKHFD150](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton BKHFD150

Catalog Number: BKHFD150

Eaton Pow-R-stock series Main circuit breaker kit, HFD circuit bkr type, Top and Bottom Mounting, Top and Bottom, Single- or three-phase, 150A



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Pow-R-Stock main breaker kit	BKHFD150
<b>UPC</b>	<b>Product Length/Depth</b>
786689030780	3.9 in
<b>Product Height</b>	<b>Product Width</b>
6 in	4.13 in
<b>Product Weight</b>	<b>Certifications</b>
5 lb	UL Listed

## defaultTaxonomyAttributeLabel

### Circuit breaker type

HFD

### Mounting

Top, bottom

### Phase

Single-phase, three-phase

### Rated operational current

150A

### Series

Pow-R-stock

## Resources

### Multimedia

[Pow-R-Line Xpert family overview](#)

### Specifications and datasheets

[Eaton Specification Sheet - BKHFD150](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)