

Eaton BKLGE600

Catalog Number: BKLGE600

Eaton Pow-R-stock series Main circuit breaker kit, LGE circuit bkr type, Top and Bottom Mounting, Top and Bottom, Single- or three-phase, 600A



General specifications

| | |
|------------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton Pow-R-Stock main breaker kit | BKLGE600 |
| UPC | Product Length/Depth |
| 786689031008 | 5.5 in |
| Product Height | Product Width |
| 12 in | 5.5 in |
| Product Weight | Certifications |
| 16 lb | UL Listed |

defaultTaxonomyAttributeLabel

Circuit breaker type

LG

Mounting

Top, bottom

Phase

Single-phase, three-phase

Rated operational current

600A

Series

Pow-R-stock

Resources

Multimedia

[Pow-R-Line Xpert family overview](#)

Specifications and datasheets

[Eaton Specification Sheet - BKLGE600](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton BKLGE600

Catalog Number: BKLGE600

Eaton Pow-R-stock series Main circuit breaker kit, LGE circuit bkr type, Top and Bottom Mounting, Top and Bottom, Single- or three-phase, 600A



General specifications

| | |
|------------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton Pow-R-Stock main breaker kit | BKLGE600 |
| UPC | Product Length/Depth |
| 786689031008 | 5.5 in |
| Product Height | Product Width |
| 12 in | 5.5 in |
| Product Weight | Certifications |
| 16 lb | UL Listed |

defaultTaxonomyAttributeLabel

Circuit breaker type

LG

Mounting

Top, bottom

Phase

Single-phase, three-phase

Rated operational current

600A

Series

Pow-R-stock

Resources

Multimedia

[Pow-R-Line Xpert family overview](#)

Specifications and datasheets

[Eaton Specification Sheet - BKLGE600](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)