



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **BIBD43FX 14-4, 2-Sided Uni-Tap** *Burndy LLC*

|                  |   |
|------------------|---|
| Catalog Number   | BIBD43FX  |
| Manufacturer     | Burndy LLC  |
| Description      | Aluminum Unitap, Double Sided Entry, #14-#4 Class B & C ,<br>#14-#6 Class G, H, I, K, Dlo, 3 Port |
| Weight per unit  | 0.1070 (lbs/each)   |
| Product Category | Large Terminals & Connectors  |

### **Features**

|                 |          |
|-----------------|----------|
| amperage rating | 85       |
| Conductor Size  | 14-4 AWG |
| Material        | Aluminum |

### **Descriptions**

|                        |   |
|------------------------|---|
| Description            | 14-4, 2-SIDED UNI-TAP   |
| extra long description | BUR BIBD43FX 14-4 TWO SIDED UNITAP,   |
| Long Description       | Aluminum UNITAP, Double Sided Entry, #14-#4 Class B & C<br>,#14-#6 Class G,H,I,K, DLO, 3 PORT   |
| Product Type           | RUN/TAP   |
| Special Features       | Features: Clear Platisol covered AL6061-T6 aluminum body,<br>Saves time, lowers installation costs, eliminates taping, Oxide<br>inhibitor pre-installed, Inhibits moisture and contaminants from<br>entering the contact area |

### **Manufacturer Information**

|                           |                |
|---------------------------|----------------|
| Brand                     | Burndy LLC     |
| GTIN                      | 00621945438712 |
| Manufacturers Part Number | BIBD43FX       |
| UPC                       | 621945438712   |

### **Taxonomies, Classifications, and Categories**

|                      |                           |
|----------------------|---------------------------|
| Category Description | TERMINAL BLOCK ACESSORIES |
| Type                 | BIBD, Multi-Port          |

### **Packaging**

|                 |       |
|-----------------|-------|
| Carton          | 1     |
| Package         | 100   |
| Weight Per each | 0.107 |

### **Uses, Certifications, and Standards**

|                    |  |
|--------------------|--|
| Application        | Tap connections and in-line splice/reductions are made quickly<br>and easily with the UNITAP™ line of connectors |
| standard           | UL 486A-486B   |
| Temperature Rating | -40° C to 135 °C   |