

Specifications

Eaton BJ34

Eaton Crouse-Hinds series XJG bonding jumper, Rigid/IMC, 4" maximum conduit movement, Used with XJG34, 1" trade size



Photo is representative

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series XJG bonding jumper
CATALOG NUMBER	BJ34
UPC	782274991870
PRODUCT LENGTH/DEPTH	20 in
PRODUCT HEIGHT	0.88 in
PRODUCT WIDTH	0.19 in
PRODUCT WEIGHT	1.35 lb

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

CONDUIT TYPE	Rigid/IMC
TRADE SIZE	1"
CONDUIT MOVEMENT - MAX	4"
SPECIAL FEATURES	Used with XJG34

Resources

BROCHURES	Crouse-Hinds series Conduit Expansion/Deflection Couplings brochure
-----------	---

CATALOGS	Crouse-Hinds series XJG Conduit Expansion Couplings for Rigid/IMC catalog page
----------	--

CERTIFICATION REPORTS	XJG Conduit Expansion Couplings for EMT and Rigid/IMC Canadian certification
-----------------------	--

CERTIFICATION REPORTS	XJG Conduit Expansion Couplings for EMT and Rigid/IMC UL certification
-----------------------	--

SPECIFICATIONS AND DATASHEETS	Expansion and Deflection Couplings Eaton Specification Sheet - BJ34
-------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.

Specifications

Eaton BJ34

Eaton Crouse-Hinds series XJG bonding jumper, Rigid/IMC, 4" maximum conduit movement, Used with XJG34, 1" trade size



Photo is representative

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series XJG bonding jumper
CATALOG NUMBER	BJ34
UPC	782274991870
PRODUCT LENGTH/DEPTH	20 in
PRODUCT HEIGHT	0.88 in
PRODUCT WIDTH	0.19 in
PRODUCT WEIGHT	1.35 lb

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

CONDUIT TYPE	Rigid/IMC
TRADE SIZE	1"
CONDUIT MOVEMENT - MAX	4"
SPECIAL FEATURES	Used with XJG34

Resources

BROCHURES	Crouse-Hinds series Conduit Expansion/Deflection Couplings brochure
-----------	---

CATALOGS	Crouse-Hinds series XJG Conduit Expansion Couplings for Rigid/IMC catalog page
----------	--

CERTIFICATION REPORTS	XJG Conduit Expansion Couplings for EMT and Rigid/IMC Canadian certification
-----------------------	--

CERTIFICATION REPORTS	XJG Conduit Expansion Couplings for EMT and Rigid/IMC UL certification
-----------------------	--

SPECIFICATIONS AND DATASHEETS	Expansion and Deflection Couplings Eaton Specification Sheet - BJ34
-------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.