

# Specifications



## Eaton BMM603-3SQ

Eaton Bussmann series BMM fuse blocks, 30 A, Three-pole, Screw/quick connect, 200 kAIC, 600 V

### General specifications

<b>PRODUCT NAME</b>	Eaton Bussmann series BMM fuse blocks
<b>CATALOG NUMBER</b>	BMM603-3SQ
<b>UPC</b>	051712486477
<b>PRODUCT LENGTH/DEPTH</b>	0.001 in
<b>PRODUCT HEIGHT</b>	0.001 in
<b>PRODUCT WIDTH</b>	0.001 in
<b>PRODUCT WEIGHT</b>	0.1 lb
<b>WARRANTY</b>	Not Applicable
<b>COMPLIANCES</b>	RoHS Compliant CE Marked
<b>CERTIFICATIONS</b>	Contact Manufacturer UL Recognized CSA Certified



Powering Business Worldwide

## Electrical rating

AMPERAGE RATING	30 A
SHORT-CIRCUIT RATING	200 kA
VOLTAGE RATING	600 V

## General information

CONNECTION	Screw/quick connect
------------	---------------------

## Physical details

NUMBER OF POLES	Three-pole
-----------------	------------

## Resources

CATALOGS	<a href="#">BMM603-3SQ~MIDGET FUSE BLOCK W/ SCREW and QC - 3 POLE</a> <a href="#">Bussmann series complete full line catalog no. 1007</a>
MULTIMEDIA	<a href="#">Bussmann series Fuseology</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - BMM603-3SQ</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications



## Eaton BMM603-3SQ

Eaton Bussmann series BMM fuse blocks, 30 A, Three-pole, Screw/quick connect, 200 kAIC, 600 V

### General specifications

<b>PRODUCT NAME</b>	Eaton Bussmann series BMM fuse blocks
<b>CATALOG NUMBER</b>	BMM603-3SQ
<b>UPC</b>	051712486477
<b>PRODUCT LENGTH/DEPTH</b>	0.001 in
<b>PRODUCT HEIGHT</b>	0.001 in
<b>PRODUCT WIDTH</b>	0.001 in
<b>PRODUCT WEIGHT</b>	0.1 lb
<b>WARRANTY</b>	Not Applicable
<b>COMPLIANCES</b>	RoHS Compliant CE Marked
<b>CERTIFICATIONS</b>	Contact Manufacturer UL Recognized CSA Certified



Powering Business Worldwide

## Electrical rating

AMPERAGE RATING	30 A
SHORT-CIRCUIT RATING	200 kA
VOLTAGE RATING	600 V

## General information

CONNECTION	Screw/quick connect
------------	---------------------

## Physical details

NUMBER OF POLES	Three-pole
-----------------	------------

## Resources

CATALOGS	<a href="#">BMM603-3SQ~MIDGET FUSE BLOCK W/ SCREW and QC - 3 POLE</a> <a href="#">Bussmann series complete full line catalog no. 1007</a>
MULTIMEDIA	<a href="#">Bussmann series Fuseology</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - BMM603-3SQ</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

