



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR1632B200 16/32C 200A 1PH MB Loadcenter

Eaton Corp

Catalog Number	BR1632B200
Manufacturer	Eaton Corp
Description	BR Style 1-Inch Loadcenter, Main Circuit Breaker, No Feed-Thru Lugs, 200A, Single-Phase, 32-Pole, 32 Circuits, 16 Spaces, 120/240V, #2/0-300 Kcmil Cu/Al At 60°C or 75°C Wire, Nema 1 Enclosure, C4 Box Size
Weight per unit	27.4 (lbs/each)
Product Category	Single Phase Main Breaker Load

Features

amperage rating	59120
Box Size	HID Floodlight
cover	Cover included
Cover Type	Cover included
dimensions	5.0000 IN X 13.0000 IN X 15.0000 IN
interrupt rating	25 kAIC
main circuit breaker	BWH
Number of Circuits	32 W
number of spaces	16 OZ
Number of Wires	Three-wire
Phase	1 PH
used with	Type BR 1-inch breakers
Voltage Rating	120/240 VAC
Wire Size	#2/0-300 kcmil Cu/Al at 60°C or 75°C

Material, Color, and Finish

Bus Material	Aluminum
Enclosure Material	Metallic

Dimensions and Weight

Size	C4
------	----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	16/32C 200A 1PH MB LOADCENTER
extra long description	ETN BR1632B200 BR style 1-inch load
Long Description	BR style 1-inch loadcenter, main circuit breaker, no feed-thru lugs, 200A, single-phase, 32-pole, 32 circuits, 16 spaces, 120/240V, #2/0-300 kcmil Cu/Al at 60°C or 75°C wire, NEMA 1 enclosure, c4 box size
Product Type	BR Style 1-Inch Loadcenter
Special Features	No feed-thru lugs

Manufacturer Information

Brand	Eaton
GTIN	00786676445351
Manufacturers Part Number	BR1632B200
UPC	786676445351

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
igcc	PLUG, NON POLARIZED TYPE; THERMOPLASTIC MATERIAL; WHITE COLOR; 1-15P CONFIGURATION; UL 1706, CSA APPROVAL; 125 V VOLTAGE RATING; 15 AMPERE CURRENT RATING; IMPACT RESISTANT; (2) 18 AWG CORD SIZE; HOMeselect[T] BRAND
Type	Main circuit breaker
unspsc code	39121101

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Weight Per each	27.4

Uses, Certifications, and Standards

Application	Power Distribution
Enclosure	NEMA 1
Mounting standard	Combination UL 67; UL 50