



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BQ2302120 BQ Quad BRKR 1-30A/2P 2-20A/1P Indep. Trip 120/240

Eaton Corp

| | |
|------------------|---|
| Catalog Number | BQ2302120 |
| Manufacturer | Eaton Corp |
| Description | Eaton BR Thermal Magnetic Circuit Breaker, Type BQ 1-Inch CTL Plug-On Circuit Breaker, Includes Rejection Tab Feature, (2) Single-Pole 20 A, (1) Two-Pole 30 A, 10 Kaic, Four-Pole, 120/240V At 30A, 120V At 20A, BQ, Independent, #14-4 Awg Cu/Al, Q28, BQ |
| Weight per unit | 0.9000 (lbs/each) |
| Product Category | Quadplex Standard Trip Plug-In |

Features

| | |
|------------------|-----------------------------------|
| dimensions | 3.0000 IN X 2.0000 IN X 3.0000 IN |
| interrupt rating | 10 kAIC |
| Poles | 4 |
| Trip Type | T194 |
| Voltage Rating | 120/240V at 30A, 120V at 20A |

Descriptions

| | |
|------------------------|--|
| Description | BQ QUAD BRKR 1-30A/2P 2-20A/1P INDEP. TRIP 120/240 |
| extra long description | ETN BQ2302120 BQ Quad 1-30A/2P 2-20 |
| Features | Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF. |
| Long Description | Eaton BR thermal magnetic circuit breaker, Type BQ 1-Inch CTL plug-on circuit breaker, Includes rejection tab feature, (2) Single-Pole 20 A, (1) Two-Pole 30 A, 10 kAIC, Four-pole, 120/240V at 30A, 120V at 20A, BQ, Independent, #14-4 AWG Cu/Al, Q28, BQ |
| Product Type | BQ Quad 1-30A/2P 2-20A/1P 120/240V 10K |
| Special Features | Includes Rejection Tab feature |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Eaton |
| GTIN | 00786676371551 |
| Manufacturers Part Number | BQ2302120 |
| UPC | 786676371551 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | Specialty Breakers (Quad, Dupl, Shunt Trip) |
| Type | Thermal magnetic circuit breakers |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Package | 6 |
| Weight Per each | 0.9 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Application | Generation - Conventional Energy - Conventional Energy Other Datacenters - IT Space: CI and Hyper Converged Marine Vessels and Equipment - Marine Vessels and Equipment - Other Generation - Renewable Energy - Alternative Energy |
| standard | UL 489, Federal Specifications Classification W-C375 |