



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR4040B200V2 1PH 200A 40/40 MB Loadcenter

Eaton Corp

| | |
|------------------|---|
| Catalog Number | BR4040B200V2 |
| Manufacturer | Eaton Corp |
| Description | BR Style Load Center, 40 Spaces, 40 Circuits, 200 A, 120/240 V Ac, 2/0 Awg to 300 Kcmil Wire Size, Metallic Material, Copper Bus Material |
| Weight per unit | 42.4 (lbs/each) |
| Product Category | Single Phase Main Breaker Load |

Features

| | |
|----------------------|-------------------------------------|
| amperage rating | 59120 |
| Box Size | D1r |
| cover | Cover included |
| Cover Type | Cover included |
| dimensions | 5.1900 IN X 14.3100 IN X 29.1300 IN |
| main circuit breaker | BWH |
| Number of Wires | Three-wire |
| Phase | 1 PH |
| used with | Type BR 1-inch breakers |

Material, Color, and Finish

| | |
|--------------------|----------|
| Enclosure Material | Metallic |
|--------------------|----------|

Dimensions and Weight

| | |
|------|-----|
| Size | D1r |
|------|-----|

Descriptions

| | |
|------------------------|-------------------------------------|
| Description | 1PH 200A 40/40 MB LOADCENTER |
| extra long description | ETN BR4040B200V2 BR style 1-inch lo |

Manufacturer Information

| | |
|------|----------------|
| GTIN | 00782114894484 |
| UPC | 782114894484 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | LOADCENTERS & COVERS |
| igcc | PLUG, NON POLARIZED TYPE; THERMOPLASTIC MATERIAL; WHITE COLOR; 1-15P CONFIGURATION; UL 1706, CSA APPROVAL; 125 V VOLTAGE RATING; 15 AMPERE CURRENT RATING; IMPACT RESISTANT; (2) 18 AWG CORD SIZE; HOMeselect[T] BRAND |
| Type | Main circuit breaker |
| unspsc code | MODULAR LINE CORD, TELEPHONE LINE EXTENSION CORD TYPE; 15 FT LENGTH IN FT; METALLIC COLOR FAMILY; SILVER MANUFACTURERS COLOR NAME; GC[T] BRAND; CONNECTOR TYPE MODULAR PLUG; CORD SIZE (6) 26 AWG |

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Weight Per each | 42.36 |

Uses, Certifications, and Standards

| | |
|-------------|--------------------|
| Application | Power Distribution |
| Enclosure | NEMA 1 |
| standard | UL 67; UL 50 |