

# Specifications



Photo is representative



## Eaton BRCAFI120

Eaton BR AFCI circuit breaker, Arc fault, 20A, 10 kAIC, Single-pole, 120V, BR, #14-4 AWG Cu/Al, Type BR Loadcenters

### General specifications

PRODUCT NAME	Eaton BR AFCI circuit breaker
CATALOG NUMBER	BRCAFI120
UPC	786685514338
PRODUCT LENGTH/DEPTH	6 in
PRODUCT HEIGHT	1.25 in
PRODUCT WIDTH	3.5 in
PRODUCT WEIGHT	0.45 lb
WARRANTY	Limited lifetime residential, 1 year commercial
COMPLIANCES	Federal Specifications Classification W-C375
CERTIFICATIONS	UL 1699

Product specifications	
USED WITH	Type BR Loadcenters
SPECIAL FEATURES	Arc fault
AMPERAGE RATING	20 A
VOLTAGE RATING	120 V
INTERRUPT RATING	10 kAIC
MAIN CIRCUIT BREAKER	BR
WIRE SIZE	#14-4 AWG Cu/Al
NUMBER OF POLES	Single-pole

Resources	
CATALOGS	<a href="#">Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - BRCAF120</a>
WARRANTY GUIDES	<a href="#">Eaton type BR circuit breaker limited warranty June 2024</a>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.  
All other trademarks are property of their respective owners.



# Specifications



Photo is representative



## Eaton BRCAFI120

Eaton BR AFCI circuit breaker, Arc fault, 20A, 10 kAIC, Single-pole, 120V, BR, #14-4 AWG Cu/Al, Type BR Loadcenters

### General specifications

PRODUCT NAME	Eaton BR AFCI circuit breaker
CATALOG NUMBER	BRCAFI120
UPC	786685514338
PRODUCT LENGTH/DEPTH	6 in
PRODUCT HEIGHT	1.25 in
PRODUCT WIDTH	3.5 in
PRODUCT WEIGHT	0.45 lb
WARRANTY	Limited lifetime residential, 1 year commercial
COMPLIANCES	Federal Specifications Classification W-C375
CERTIFICATIONS	UL 1699

Product specifications	
USED WITH	Type BR Loadcenters
SPECIAL FEATURES	Arc fault
AMPERAGE RATING	20 A
VOLTAGE RATING	120 V
INTERRUPT RATING	10 kAIC
MAIN CIRCUIT BREAKER	BR
WIRE SIZE	#14-4 AWG Cu/Al
NUMBER OF POLES	Single-pole

Resources	
CATALOGS	<a href="#">Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - BRCAF120</a>
WARRANTY GUIDES	<a href="#">Eaton type BR circuit breaker limited warranty June 2024</a>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.  
All other trademarks are property of their respective owners.

