



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR4242L225G 42/42C 225A Mlo Loadcenter W/Ground

Eaton Corp

Catalog Number	BR4242L225G
Manufacturer	Eaton Corp
Description	Main Lug Load Center, 42 Spaces, 42 Circuits, 225 A, 120/240 V Ac, #1 Awg to 300 Kcmil Wire Size, Metallic Material, Aluminum Bus Material
Weight per unit	37.0 (lbs/each)
Product Category	Single Phase Main Lug Load Cen

Features

amperage rating	225 Im
Box Size	5 in
cover	Cover not included
Cover Type	Cover not included
dimensions	5.2000 IN X 14.3000 IN X 39.0000 IN
main circuit breaker	CEMAT RSRT9 V7.0 OS SOFTWARE
number of spaces	42 WTT
Number of Wires	Three-wire
Phase	1 PH
used with	Type BR 1-inch breakers

Material, Color, and Finish

Enclosure Material	Metallic
--------------------	----------

Dimensions and Weight

Size	5 kVA kVA
------	-----------

Descriptions

Description	42/42C 225A MLO LOADCENTER W/GROUND
extra long description	ETN BR4242L225G Eaton BR style 1-in
Special Features	Current design

Manufacturer Information

GTIN	00782116946396
UPC	782116946396

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
igcc	PLUG, NON POLARIZED TYPE; THERMOPLASTIC MATERIAL; WHITE COLOR; 1-15P CONFIGURATION; UL 1706, CSA APPROVAL; 125 V VOLTAGE RATING; 15 AMPERE CURRENT RATING; IMPACT RESISTANT; (2) 18 AWG CORD SIZE; HOMeselect[T] BRAND
Type	MAIN LUG
unspsc code	39121101



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Status Inactive

Packaging

Carton 1

Weight Per each 37

Uses, Certifications, and Standards

Enclosure NEMA 1

Mounting Surface mounting

standard UL 67; UL 50