

Eaton BRP115AF

Catalog Number: BRP115AF

Eaton BR AFCI circuit breaker, AFCI Combination circuit breaker, UL only, 15 A, 10 kAIC, Single-pole, 120 V, BR, Plug-on, #14-8 AWG Cu/Al, Type BR Loadcenters, Plug-on neutral



General specifications

Product Name	Catalog Number
Eaton BR AFCI circuit breaker	BRP115AF
UPC	Product Length/Depth
786689041014	2.56 in
Product Height	Product Width
1.1 in	1 in
Product Weight	Certifications
0.38 lb	UL Listed

Product specifications

Used with

Type BR Loadcenters

Type

AFCI Combination circuit breaker

Special features

UL only

Amperage Rating

15 A

Voltage rating

120 V

Neutral

Plug-on neutral

Interrupt rating

10 kAIC

Main circuit breaker

BR

Connection

Plug-on

Wire size

#14-8 AWG Cu/Al

Number of poles

Single-pole

Resources

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton BRP115AF

Catalog Number: BRP115AF

Eaton BR AFCI circuit breaker, AFCI Combination circuit breaker, UL only, 15 A, 10 kAIC, Single-pole, 120 V, BR, Plug-on, #14-8 AWG Cu/Al, Type BR Loadcenters, Plug-on neutral



General specifications

Product Name	Catalog Number
Eaton BR AFCI circuit breaker	BRP115AF
UPC	Product Length/Depth
786689041014	2.56 in
Product Height	Product Width
1.1 in	1 in
Product Weight	Certifications
0.38 lb	UL Listed

Product specifications

Used with

Type BR Loadcenters

Type

AFCI Combination circuit breaker

Special features

UL only

Amperage Rating

15 A

Voltage rating

120 V

Neutral

Plug-on neutral

Interrupt rating

10 kAIC

Main circuit breaker

BR

Connection

Plug-on

Wire size

#14-8 AWG Cu/Al

Number of poles

Single-pole

Resources

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia