



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BRP30B200RV25 BR Pon Loadctr 200A Main BRKR 30 Space N3R

Eaton Corp

Catalog Number	BRP30B200RV25
Manufacturer	Eaton Corp
Description	BR Plug-On Neutral Loadcenter Value Pack, 200A, Main Breaker, 30 Spaces, Nema 3R W/ (2) BR120 & (1) BR230
Weight per unit	27.0 (lbs/each)
Product Category	Single Phase Main Breaker Load

Features

amperage rating	200
Cover Type	Cover included
interrupt rating	25
number of spaces	30
Phase	1
Voltage Rating	120/240 V

Dimensions and Weight

Depth	34.12
Height	5.5
Size	X6
Width	14.31

Descriptions

Description	BR PON LOADCNTR 200A MAIN BRKR 30 SPACE N3R
extra long description	ETN BRP30B200RV25 BR PON LC,200A, M
Features	Specially designed for easy installation, Eaton's BR 1-inch load centers house the branch circuit breakers and the wiring required to distribute power to individual circuits. They serve as main breaker for service entrances or as main lug when adding circuits to existing service. The main breaker protects the entire panel and can be used as a service disconnect. The branch breakers protect the wires leading to individual electrical loads such as fixtures and outlets.
Long Description	BR plug-on neutral loadcenter value pack, 200A, main breaker, 30 spaces, NEMA 3R w/ (2) BR120 & (1) BR230
Product Type	BR Pon LC, 200A, MCB, 30 Space, N3R
Special Features	Value pack

Manufacturer Information

Brand	Eaton
GTIN	00786689058432
Manufacturers Part Number	BRP30B200RV25
UPC	786689058432



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description LOADCENTERS & COVERS

Type Main breaker loadcenter

Packaging

Carton 1

Weight Per each 27

Uses, Certifications, and Standards

Application Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels
and OEMs

Mounting Combination Mount

standard UL 50,UL 67