



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BRP20B125 BR Pon Loadcntr 125A Main BRKR 20 Space

Eaton Corp

| | |
|------------------|---|
| Catalog Number | BRP20B125 |
| Manufacturer | Eaton Corp |
| Description | Eaton Plug-On Neutral Main Circuit Breaker Loadcenter, X3, Aluminum, Cover Included, Nema 1, Metallic, 10KAIC, BR2125, 40 Circuits, Single Pole, 20 Spaces, Two Hots, A Neutral, and A Ground, Single-Phase, Gray, Combination, Nema 1, Type BR 1-Inch Breakers |
| Weight per unit | 21.6 (lbs/each) |
| Product Category | Single Phase Main Breaker Load |

Features

| | |
|------------------|-------------------------------------|
| amperage rating | 125 A |
| Cover Type | Cover included |
| dimensions | 23.0000 IN X 14.3100 IN X 3.8800 IN |
| interrupt rating | 10 kAIC |
| number of spaces | 20 |
| Phase | Single-phase |
| Voltage Rating | 120/240 V |
| Wattage | Single-pole |

Dimensions and Weight

| | |
|--------|---------|
| Depth | 23.0000 |
| Height | 3.8800 |
| Size | X3 |
| Width | 14.3100 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | BR PON LOADCNTR 125A MAIN BRKR 20 SPACE |
| extra long description | ETN BRP20B125 BR PON LC,125A, MCB, |
| Features | Specially designed for easy installation, Eaton's BR 1-inch load centers house the branch circuit breakers and the wiring required to distribute power to individual circuits. They serve as main breaker for service entrances or as main lug when adding circuits to existing service. The main breaker protects the entire panel and can be used as a service disconnect. The branch breakers protect the wires leading to individual electrical loads such as fixtures and outlets. |
| Long Description | Eaton Plug-on neutral main circuit breaker loadcenter,X3,Aluminum,Cover included,NEMA 1,Metallic,10kAIC,BR2125,40 circuits,Single pole,20 spaces,Two hots, a neutral, and a ground,Single-phase,Gray,Combination,NEMA 1,Type BR 1-inch breakers |
| Product Type | BR Pon LC, 125A, MCB, 20 Space |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Eaton |
| GTIN | 00786689053161 |
| Manufacturers Part Number | BRP20B125 |
| UPC | 786689053161 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------|
| Category Description | LOADCENTERS & COVERS |
| Type | Main breaker loadcenter |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 21.6 |

Uses, Certifications, and Standards

| | |
|-------------------|---|
| Application | Elec Assemblies, Panels & EOEM - Electrical Assemblies, Panels and EOEMsResidential Bldgs & Facilities - Residential Bldgs & Facilities - Other |
| Mounting standard | Combination Mount UL 67,UL 50 |