



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## BT9LHL 30.7" 120LB NTRL Dome-Top Barb CBL Tie

*Panduit Corporation*

Catalog Number	BT9LHL
Manufacturer	Panduit Corporation
Description	The BT9LH-L Dome-Top® Barb Ty, Features A Unique Patented Design With Its Round Smooth Edges. Paired With The Stainless-Steel Locking Barb, These Cable Ties Provide Consistent Performance, Reliability and Infinite Adjustability Through The Entire Bundle Range. Light-Heavy Cross Section, 30.7" (780MM) Length. Appropriate For Indoor Use, Made Of Nylon 6.6, Are Natural In Color and Come In Packages Of 50.
Weight per unit	1.4 (lbs/each)
Product Category	Cable Ties & Wraps

### Features

media	Yes
Tensile Strength	120

### Dimensions and Weight

Length	30.7
Thickness	0.07

### Descriptions

Description	30.7" 120LB NTRL DOME-TOP BARB CBL TIE
extra long description	PAN BT9LH-L Dome-Top® BT9LH-L Barb
Long Description	The BT9LH-L Dome-Top® barb ty, features a unique patented design with its round smooth edges. Paired with the stainless-steel locking barb, these cable ties provide consistent performance, reliability and infinite adjustability through the entire bundle range. Light-Heavy cross section, 30.7" (780mm) length. Appropriate for Indoor use, made of Nylon 6.6, are natural in color and come in packages of 50.
Product Type	Dome-Top® BT9LH-L Barb Tie, PA6.6, 30.7"L, 120LB, PK50
Special Features	Indoor

### Manufacturer Information

Brand	Panduit®
GTIN	00074983412976
Manufacturers Part Number	BT9LH-L
UPC	074983412976

### Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Cable Tie



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Availability

minimum qty ..... 50

## Packaging

Carton ..... 50

Package ..... 500

Weight Per each ..... 1.35

## Uses, Certifications, and Standards

standard ..... UL 62275 (File E56854), CSA-C22.2 No. 62275 (File 31212), Cert  
05968/C0, BV File ACE 14/601/01 Product Code: 2535H,  
89/60111 (E3), 11130200, QPL-AS23190, RoHS Compliant