



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BSPMA3480WYGR 3P 277/480 Wye

Bussmann Fuses

| | |
|------------------|---|
| Catalog Number | BSPMA3480WYGR |
| Manufacturer | Bussmann Fuses |
| Description | Eaton Bussmann Series BSPM Series Surge Arrestor, Technology Type Mov, 277/480 V, Surge Arrestor, Thermoplastic, UL94V2, 50/60 HZ, 200 Kilo Ampere, Thermoplastic, Remote Contact |
| Weight per unit | 0.7500 (lbs/each) |
| Product Category | Surge Suprsr-Prot Dev-LN Condi |

Features

| | |
|--------------------|----------------|
| Material | Thermoplastic |
| type of indicators | Remote contact |
| Voltage Rating | 277/480 V |

Dimensions and Weight

| | |
|--------|------|
| Depth | 2.13 |
| Height | 3.54 |
| Width | 2.56 |

Descriptions

| | |
|------------------------|---|
| Description | 3P 277/480 WYE |
| extra long description | BUSS BSPMA3480WYGR 277/480 Wye, 3P |
| Features | Surge protective devices/surge protectors |
| Long Description | Eaton Bussmann series BSPM series surge arrestor, Technology type MOV, 277/480 V, Surge arrestor, Thermoplastic, UL94V2, 50/60 Hz, 200 Kilo Ampere, Thermoplastic, Remote Contact |
| Product Type | 277/480 Wye, 3P |
| Special Features | Technology type MOV |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Eaton |
| GTIN | 00051712709095 |
| Manufacturers Part Number | BSPMA3480WYGR |
| UPC | 051712709095 |

Taxonomies, Classifications, and Categories

| | |
|------|----------------|
| Type | Surge arrestor |
|------|----------------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 0.75 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs |
| Mounting | DIN rail (top hat rail) 35 mm |
| standard | UL 94V0 ,UL Listed,Contact factory,RoHS Compliant |