



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## C25BNB220T Compact 2P 20A Cont SCR Term Quad QC 24VAC Coil *Eaton Corp*

Catalog Number	C25BNB220T
Manufacturer	Eaton Corp
Description	Eaton Definite Purpose Contactor, Quick, 20A, 277 Vac, 60 HZ, Open With Metal Mounting Plate, Compact, Two-Pole, 20A, Contactor, Two-Pole, Power Terminals: Binding Head Screw and Quick Con, Non-Reversing
Weight per unit	0.6000 (lbs/each)
Product Category	Definite Purpose Contactors

### Features

connection	Quick
dimensions	2.3200 IN X 1.9700 IN X 3.1900 IN
Enclosure Type	Open with metal mounting plate

### Dimensions and Weight

Depth	2.32
Height	3.19
Width	1.97

### Descriptions

Description	COMPACT 2P 20A CONT SCR TERM QUAD QC 24VAC COIL
extra long description	ETN C25BNB220T COMPCT 2P 20A CONT S
Features	Definite purpose contactors and starters are electrically operated switching devices specifically designed for the heating, ventilation, air conditioning and refrigeration (HVAC) industry.
Long Description	Eaton definite purpose contactor, Quick, 20A, 277 Vac, 60 Hz, Open with metal mounting plate, Compact, two-pole, 20A, Contactor, Two-pole, Power terminals: Binding head screw and quick con, Non-reversing
Product Type	Compct 2P 20A Cont SCR Term 4QC 24vcoil

### Manufacturer Information

Brand	Eaton
GTIN	00786685115986
Manufacturers Part Number	C25BNB220T
UPC	786685115986

### Taxonomies, Classifications, and Categories

Category Description	FREEDOM/NEMA STYLE
Type	Definite purpose contactor



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	5
Weight Per each	0.6

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
standard	UL Recognized, CSA Certified, RoHS Compliant