



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C12N 12-10AWG Closed End Wire Nyl Conn W/CRMP SLV

Nsi Industries

Catalog Number	C12N
Manufacturer	Nsi Industries
Description	The Easy-Twist C12-N 50-Count Pack Of Nylon Closed-End Wire Connectors Are Designed For Use On Pre-Insulated Wires In The 12-10 Awg Size Range. Theyâ€™re UL-Certified As Self-Extinguishing and Rated For A Maximum Temperature Of 105Ëš Celsius (221Ëš Fahrenheit). The Closed-End Nylon Connector Features An Internal Metal Crimp Sleeve That Can Be Tightened Over Twisted Pre-Insulated Wires to Form A Safe and Secure Join. Their Compact Design Is Useful For Applications In Tight Areas or Anywhere Else You Need to
Weight per unit	N/A
Product Category	20240531150518

Features

Warranty	1 YEAR
Wire Size	22-10 AWG
Wire Type	CU Wire Only

Descriptions

Description	12-10AWG CLOSED END WIRE NYL CONN W/CRMP SLV
extra long description	NSI C12-N CU CMP Splice Long 3 AWG
Features	Connecting wires is faster and easier than ever with the professional performance features of Easy-Twist wire connectors from NSI. These closed-end connectors feature a corrosion and chemical resistant nylon cover over a metal crimp cap wire terminal. These connectors are easy to install; simply twist your wires together to form a connection, then slide the closed end butt connector over the pigtail and crunch it tight with adjustable pliers or a specialized crimping tool. We designed these closed-end conn
Long Description	The Easy-Twist C12-N 50-Count Pack of Nylon Closed-End Wire Connectors are designed for use on pre-insulated wires in the 12-10 AWG size range. Theyâ€™re UL-certified as self-extinguishing and rated for a maximum temperature of 105Ëš Celsius (221Ëš Fahrenheit). The closed-end nylon connector features an internal metal crimp sleeve that can be tightened over twisted pre-insulated wires to form a safe and secure join. Their compact design is useful for applications in tight areas or anywhere else you need to
Product Type	Cu CMP Splice Long 3 Awg



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	NSi
GTIN	00662381362629
Manufacturers Part Number	C12-N
UPC	662381362629

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
----------------------	-----------

Availability

minimum qty	50
-------------	----

Packaging

Carton	50
Weight Per each	0