



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## C25DND230T Open N-R 2P 30A DP Cont SCR/PP W/QC Term 24VAC Coi Eaton Corp

Catalog Number	C25DND230T
Manufacturer	Eaton Corp
Description	Eaton Definite Purpose Contactor, Mounting Plate, Quick, Pressure Plate Quick Connect (Side-By-Side), 12 VDC, Open With Metal Mounting Plate, 15-50A, Two- and Three-Pole, 40A, Contactor, Two-Pole, Global Listed, D1, Screw, Non-Reversing
Weight per unit	1.2 (lbs/each)
Product Category	Definite Purpose Contactors

### Features

Enclosure Type	Open with metal mounting plate
induct amp/res amp rating	30/40
Voltage Rating	24

### Dimensions and Weight

Depth	3.35
Height	2.5
Width	2.4

### Descriptions

Description	OPEN N-R 2P 30A DP CONT SCR/PP W/QC TERM 24VAC COI
extra long description	ETN C25DND230T OP N-R 2P 30ADPCNT S
Features	Definite purpose contactors and starters are electrically operated switching devices specifically designed for the heating, ventilation, air conditioning and refrigeration (HVAC) industry.
Long Description	Eaton definite purpose contactor, Mounting plate, Quick, Pressure plate quick connect (side-by-side), 12 Vdc, Open with metal mounting plate, 15-50A, two- and three-pole, 40A, Contactor, Two-pole, Global listed, D1, Screw, Non-reversing
Product Type	Op N-R 2P 30ADPCNT SCR/PP W/Qc24ac

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782116300372
Manufacturers Part Number	C25DND230T
UPC	782116300372

### Taxonomies, Classifications, and Categories

Category Description	DP CONTACTORS
Type	Definite purpose contactor



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	1.19

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
standard	UL Recognized, CSA Certified, RoHS Compliant