



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C25DND325A Pen N-R 3P 25A DP Cont SCR/PP W/QC Term 120VAC Coi *Eaton Corp*

Catalog Number	C25DND325A
Manufacturer	Eaton Corp
Description	Eaton Definite Purpose Contactor, Quick, 25A, 110-120 Vac, 50/60 HZ, Open With Metal Mounting Plate, 15-50A, Two- and Three-Pole, 25A, Contactor, Three-Pole, 35A, Screw/Pressure Plate and Quick Connect Terminal (Side-By-Side), Non-Reversing
Weight per unit	1.2 (lbs/each)
Product Category	Definite Purpose Contactors

Features

Enclosure Type	Open with metal mounting plate
----------------	--------------------------------

Dimensions and Weight

Depth	3.35
Height	2.5
Width	2.4

Descriptions

Description	PEN N-R 3P 25A DP CONT SCR/PP W/QC TERM 120VAC COI
extra long description	ETN C25DND325A PEN N-R 3P 25ADPCNT
Features	Definite purpose contactors and starters are electrically operated switching devices specifically designed for the heating, ventilation, air conditioning and refrigeration (HVAC) industry.
Long Description	Eaton definite purpose contactor, Quick, 25A, 110-120 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and three-pole, 25A, Contactor, Three-pole, 35A, Screw/pressure plate and quick connect terminal (side-by-side), Non-reversing
Product Type	Pen N-R 3P 25ADPCNT SCR/PP W/Qc120ac

Manufacturer Information

Brand	Eaton
GTIN	00782116300501
Manufacturers Part Number	C25DND325A
UPC	782116300501

Taxonomies, Classifications, and Categories

Category Description	DP CONTACTORS
Type	Definite purpose contactor

Packaging

Carton	1
Weight Per each	1.19



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels
and OEMs

standard

CSA Certified,UL Recognized,RoHS Compliant