



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## C25BNB230C Compact 2P 30A Cont SCR Term Quad QC 480VAC Coil

Eaton Corp

Catalog Number	C25BNB230C
Manufacturer	Eaton Corp
Description	Eaton Definite Purpose Contactor, Quick, 30A, 208-240 Vac, 50/60 HZ, Open With Metal Mounting Plate, Compact, Two-Pole, 30A, Contactor, Two-Pole, 40A, Binding Head Screw and Quick Connect Terminals (Side-By-Side), Non-Reversing
Weight per unit	0.6000 (lbs/each)
Product Category	Definite Purpose Contactors

### Features

Enclosure Type	Open with metal mounting plate
----------------	--------------------------------

### Dimensions and Weight

Depth	2.32
Height	3.19
Width	1.97

### Descriptions

Description	COMPACT 2P 30A CONT SCR TERM QUAD QC 480VAC COIL
extra long description	ETN C25BNB230C COMPCT 2P 30A CONT S
Features	Definite purpose contactors and starters are electrically operated switching devices specifically designed for the heating, ventilation, air conditioning and refrigeration (HVAC) industry.
Long Description	Eaton definite purpose contactor, Quick, 30A, 208-240 Vac, 50/60 Hz, Open with metal mounting plate, Compact, two-pole, 30A, Contactor, Two-pole, 40A, Binding head screw and quick connect terminals (side-by-side), Non-reversing
Product Type	Compct 2P 30A Cont SCR TRM 4QC 480vcoil

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786685116044
Manufacturers Part Number	C25BNB230C
UPC	786685116044

### Taxonomies, Classifications, and Categories

Category Description	DP CONTACTORS
Type	Definite purpose contactor

### Packaging

Carton	1
Weight Per each	0.6



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels  
and OEMs

standard

UL Recognized, CSA Certified, RoHS Compliant